



HEAVY-DUTY ACCESSORIES

GUARANTEED TOUGH.

WOOD & METAL DRILLING (continued)

TITANIUM SPLIT POINT DRILL BITS



CAT #	QTY./CARD	DIA. INCHES	DIA. DECIMAL	DRILLING DEPTH	OVERALL LENGTH
DW1304	1	1/16"	.0625"	.88"	1.88"
DW1305	1	5/64"	.0781"	1.00"	2.00"
DW1306	1	3/32"	.0938"	1.25"	2.25"
DW1307	1	7/64"	.1094"	1.50"	2.62"
DW1308	1	1/8"	.1250"	1.62"	2.75"
DW1309	1	9/64"	.1406"	1.75"	2.88"
DW1310	1	5/32"	.1562"	2.00"	3.12"
DW1311	1	11/64"	.1719"	2.12"	3.25"

CAT #	QTY./CARD	DIA. INCHES	DIA. DECIMAL	DRILLING DEPTH	OVERALL LENGTH
DW1312	1	3/16"	.1875"	2.31"	3.50"
DW1313	1	13/64"	.2031"	2.44"	3.62"
DW1314	1	7/32"	.2188"	2.50"	3.75"
DW1315	1	15/64"	.2344"	2.62"	3.88"
DW1316	1	1/4"	.2500"	2.75"	4.00"
DW1320	1	5/16"	.3125"	3.19"	4.50"
DW1324	1	3/8"	.3750"	3.62"	5.00"
DW1328*	1	7/16"	.4375"	4.06"	5.50"
DW1332*	1	1/2"	.5000"	4.50"	6.00"

TITANIUM SPLIT POINT DRILL BIT SET

CAT #	DESCRIPTION	INCLUDES
DW1363	13 Pc. Titanium Split Point Drill Bit Set	(2) 1/16", 5/64", (2) 3/32", 7/64", (2) 1/8", 9/64", 5/32", 3/16", 7/32", 1/4", TOUGH CASE® Container



COBALT PILOT POINT® DRILL BITS



CAT #	QTY./CARD	BULK	BULK BAG	DIA. INCHES	DIA. DECIMAL	DRILLING DEPTH	OVERALL LENGTH
DW1204	1	DW1204B	12	1/16"	.0625"	.88"	1.88"
DW1205	1	DW1205B	12	5/64"	.0781"	1.00"	2.00"
DW1206	1	DW1206B	12	3/32"	.0938"	1.25"	2.25"
DW1207	1	DW1207B	12	7/64"	.1094"	1.50"	2.62"
DW1208	1	DW1208B	12	1/8"	.1250"	1.62"	2.75"
DW1209	1	DW1209B	12	9/64"	.1406"	1.75"	2.88"
DW1210	1	DW1210B	12	5/32"	.1562"	2.00"	3.12"
DW1211	1	DW1211B	12	11/64"	.1719"	2.12"	3.25"
DW1212	1	DW1212B	12	3/16"	.1875"	2.31"	3.50"
DW1213	1	DW1213B	12	13/64"	.2031"	2.44"	3.62"
DW1214	1	DW1214B	12	7/32"	.2188"	2.50"	3.75"
DW1215	1	DW1215B	12	15/64"	.2344"	2.62"	3.88"
DW1216	1	DW1216B	12	1/4"	.2500"	2.75"	4.00"
-	-	DW1217B	12	17/64"	.2656"	2.88"	4.12"
-	-	DW1218B	12	9/32"	.2812"	2.94"	4.25"

CAT #	QTY./CARD	BULK	BULK BAG	DIA. INCHES	DIA. DECIMAL	DRILLING DEPTH	OVERALL LENGTH
-	-	DW1219B	12	19/64"	.2969"	3.06"	4.38"
DW1220	1	DW1220B	6	5/16"	.3125"	3.19"	4.50"
-	-	DW1221B	6	21/64"	.3281"	3.31"	4.62"
-	-	DW1222B	6	11/32"	.3438"	3.44"	4.75"
-	-	DW1223B	6	23/64"	.3594"	3.50"	4.88"
DW1224	1	DW1224B	6	3/8"	.3750"	3.62"	5.00"
-	-	DW1225B*	6	25/64"	.3906"	3.75"	5.12"
-	-	DW1226B*	6	13/32"	.4062"	3.88"	5.25"
-	-	DW1227B*	6	27/64"	.4219"	3.94"	5.50"
DW1228*	1	DW1228B*	6	7/16"	.4375"	4.06"	5.82"
-	-	DW1229B*	6	29/64"	.4531"	4.19"	5.75"
-	-	DW1230B*	6	15/32"	.4688"	4.31"	3.88"
-	-	DW1231B*	6	31/64"	.4844"	4.38"	5.88"
DW1232*	1	DW1232B*	6	1/2"	.5000"	4.5"	6.00"

*3/8" reduced shank

COBALT PILOT POINT® DRILL BIT SETS

CAT #	DESCRIPTION	INCLUDES
DW1263	14 Pc. Cobalt Pilot Point Drill Bit Set	(2) 1/16", 5/64", 3/32", 7/64", (2) 1/8", 9/64", 5/32", 3/16", 7/32", 1/4", 5/16", 3/8", TOUGH CASE® Container
DW1269	29 Pc. Cobalt Pilot Point Drill Bit Set	1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 11/64", 3/16", 13/64", 7/32", 15/64", 1/4", 17/64", 9/32", 19/64", 5/16", 21/64", 11/32", 23/64", 3/8", 25/64", 13/32", 27/64", 7/16", 29/64", 15/32", 31/64", 1/2", Metal Index Container



DW1269

STEP DRILL BITS

CAT #	DESCRIPTION	# OF HOLES	SHANK SIZE	MAX. MAT. THICKNESS
Self Starting				
DW1783	1/8" - 1/2" by 1/32"	13	1/4"	1/8"
DW1784	3/16" - 1/2" by 1/16"	6	1/4"	3/8"
DW1785	1/4" - 3/4" by 1/16"	9	3/8"	1/8"
DW1786	3/16" - 7/8" by 1/16"	12	3/8"	1/8"
DW1787	7/8", 1-1/8", 1-3/8"	3	1/2"	3/16"
DW1788	3/8", 1/2"	2	1/4"	3/16"
DW1789	7/8", 1-1/8"	2	1/2"	1/8"
DW1790	7/8"	1	3/8"	-

CAT #	DESCRIPTION	# OF HOLES	SHANK SIZE	MAX. MAT. THICKNESS
Self Starting (continued)				
DW1793	4, 5, 6, 7, 8, 9, 10, 11, 12mm	9	1/4"	5mm
DW1795	6, 8, 10, 12, 14, 16, 18mm	7	3/8"	5mm
Hole Enlarging				
DW1791	9/16" - 1" by 1/16"	8	1/2"	1/8"
DW1792	13/16" - 1-3/8" by 1/16"	10	1/2"	1/8"
DW1794	14, 16, 18, 20, 22, 24, 25mm	7	1/2"	5mm
DW1796	20, 22, 24, 26, 28, 30, 32, 34mm	8	1/2"	5mm



1-800-4 DEWALT

Text "DEWALT" to 32075 to be the first to know about anything DeWALT