



# POWER TOOLS



## RECIPROCATING SAWS



SPECIFICATIONS	DW311K	DW310K	DW304PK
Amps	13.0 Amps	12.0 Amps	10.0 Amps
Strokes/Min	0-2,700 spm	0-2,700 spm	0-2,800 spm
Stroke Length	1-1/8"	1-1/8"	1-1/8"
Keyless Blade Clamp	Twist	Twist	Lever
4-Position Blade Clamp	No	No	Yes
Adjustable Shoe	Yes	Yes	Fixed
Variable-Speed Trigger	Yes	Yes	Yes
Variable-Speed Dial	Yes	No	No
Orbital Action	Yes	No	No
Anti-Slip Comfort Grip	Yes	No	No

## CIRCULAR SAWS



SPECIFICATIONS	DW384	DW364	DW369CSK	DW368	DW5535/ DW5535T
Amps	15.0 Amps	15.0 Amps	15.0 Amps	15.0 Amps	15.0 Amps
Max Watts Out	2,075 W	2,075 W	2,200 W	2,200 W	2,100 W
No Load Speed	5,800 rpm	5,800 rpm	5,800 rpm	5,800 rpm	4,800 rpm
Bevel Capacity	50°	50°	56°	56°	53°
Bevel Stops	N/A	N/A	45° / 22.5°	45° / 22.5°	45° / 22.5°
Rear Pivot	Yes	Yes	N/A	N/A	No
Electric Brake	Yes	Yes	Yes	N/A	No
Blade Diameter	8-1/4"	7-1/4"	7-1/4"	7-1/4"	7-1/4"
Depth Of Cut At 90°	2-15/16"	2-7/16"	2-3/8"	2-3/8"	2-7/16"
Depth Of Cut At 45°	2-1/4"	1-7/8"	1-3/4"	1-3/4"	1-7/8"

## JIG SAWS



SPECIFICATIONS	DW331K	DW317K
Amps	6.5 Amps	5.5 Amps
Strokes/Min	500-3,100 spm	0-3,100 spm
Stroke Length	1"	1"
Keyless Blade Clamp	Yes	Yes
Dust Blower	Yes	N/A
Orbital Action	4-position	4-position
Tool Weight	6.4 lbs	6.2 lbs



## SCROLL SAWS



SPECIFICATIONS	DW788	DW7880	DW7881
Amps	1.3 Amps		
Strokes/Min	400-1,750 spm		
Stroke Length	3/4"		
Depth of Cut (inches)	2"		
Tool Weight	56 lbs		