



**POWER TOOLS**

**ROUTERS**



1.25 HP Max Torque Variable Speed Compact Router with LED's



1.25 HP Max Torque Variable Speed Compact Router Combo Kit with LED's



1-3/4 HP (Max. Motor HP) Fixed Base / Plunge Router Combo Kit



1-3/4 HP (Max. Motor HP) Fixed Base Router

SPECIFICATIONS	DWP611	DW611PK	DW616PK	DW616/K/M
Amps	7.0 Amps	7.0 Amps	11.0 Amps	11.0 Amps
Horsepower	1-1/4 HP	1-1/4 HP	1-3/4 HP	1-3/4 HP
No Load Speed	16,000-27,000 rpm	16,000-27,000 rpm	24,500 rpm	24,500 rpm
Collet Diameter	1/4"	1/4"	1/2", 1/4"	1/2", 1/4"
Runge Stroke	N/A	2"	2-1/2"	N/A
Depth Stop	Micro-fine Ring	5	Micro-fine Ring	Micro-fine Ring
Base Dimension	4"	4" (standard), 4-3/8" x 5-3/4" (plunge)	6"	6"
Spindle Lock	Yes - 12 position	Yes - 12 position	No	No
Tool Weight	5.5 lbs	8.0 lbs	10.0 lbs	7.1 / 7.1 / 5.5lbs



2-1/4 HP (Max. Motor HP) EVS D-Handle Router w/ Soft Start



2-1/4 HP (Max. Motor HP) EVS Fixed Base Router w/ Soft Start



2-1/4 HP (Max. Motor HP) EVS Fixed Base / Plunge Router Combo Kit w/ Soft Start



2-1/4 HP (Max. Motor HP) Three Base Router Kit

SPECIFICATIONS	DW618D	DW618/K/M	DW618PK	DW618B3
Amps	12.0 Amps	12.0 Amps	12.0 Amps	12.0 Amps
Horsepower	2-1/4 HP	2 1/4 HP	2-1/4 HP	2-1/4 HP
No Load Speed	8,000-24,000 rpm	8,000-24,000 rpm	8,000-24,000 rpm	8,000-24,000 rpm
Collet Diameter	1/2", 1/4"	1/2", 1/4"	1/2", 1/4"	1/2", 1/4"
Runge Stroke	N/A	N/A	2-1/2"	2-1/2"
Depth Stop	Micro-fine Ring	Micro-fine Ring	Micro-fine Ring / 3 Stage Turret Stop	Micro-fine Ring / 3 Stage Turret Stop
Base Dimension	6"	6"	6"	6"
Spindle Lock	Yes	Yes	Yes	Yes
Tool Weight	8.2 lbs	7.2 / 7.2 / 5.6 lbs	10.1 lbs	10.1 lbs



3 HP (Max. Motor HP) EVS Plunge Router



2 HP (Max. Motor HP) EVS Plunge Router

SPECIFICATIONS	DW625	DW621/K
Amps	15.0 Amps	10.0 Amps
Horsepower	3 HP	2 HP
No Load Speed	8,000-22,000 rpm	8,000-24,000 rpm
Collet Diameter	1/2", 1/4"	1/2", 1/4"
Runge Stroke	2-7/16"	2-1/8"
Depth Stop	3 Stage Turret Stop	3 Stage Turret Stop
Base Dimension	5-5/8 x 6-11/16"	4-5/16 x 6-1/4"
Spindle Lock	Yes	Yes
Tool Weight	11.2 lbs	9.0 lbs

**FOR DUST EXTRACTION TOOLS**



PAGE 34

**ROUTER ACCESSORIES**

DNP613 – Round Sub Base for Compact Router	DW6183 – D-Handle Base for DW616/618	DW6913 – Universal Edge Guide with Dust Collection
DNP614 – Compact Router D-Shaped Sub Base	DW6184 – Fixed Base for DW616/DW618	DW6966 – Fine Depth Adjuster
DNP615 – Compact Router Dust Collection Adapter for Fixed Base	DW6188 – Template Guide Set	D26671 – Standard Base**
DNP616 – Compact Router Dust Collection Adapter for Plunge Base	DWP620 – TrackSaw Router Adapter	D26672 – Tilt Base
DNP617 – Centering Cone for Fixed Base Compact Router	DW6902 – 1/4" Collet for use with DW625	D26673 – Offset Base
DNP618 – Edge Guide for Fixed Base Compact Router	DW6904 – 3/8" Collet for use with DW625	
DW6182 – Plunge Base for DW616/DW618	DW6905 – 1/2" Collet for use with DW625	