



Dependable Power for Any Application

Product Datasheet

575Δ Primary Volts - 460Y/266 Secondary Volts - 3Ø Drive Isolation Transformer - Three Phase

Catalog #: DTHB0142S



PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Aluminum foil windings
- Copper wire terminations
- Wound/Distributed core construction
- Covered under Acme's 10 year limited warranty
- Optional Thermal Switch - part # PL79900
- Optional wall mounting kit - part # PL79911

BENEFITS

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

| | |
|-----------------------|----------|
| kVA: | 14.00 |
| Primary Voltage: | 575Δ |
| Secondary Voltage: | 460Y/266 |
| Frequency: | 60 Hz |
| ANFC Taps: | 1 |
| BNFC Taps: | 1 |
| Taps % Steps: | 5% |
| Max Temperature Rise: | 115°C |
| UL Insulation Class: | 180°C |

PRODUCT MEASUREMENTS

| | |
|------------------|--------------|
| Height (In./cm): | 18.86 (47.9) |
| Width (In./cm): | 20.3 (51.6) |
| Depth (In./cm): | 9.03 (22.9) |

CONFIGURATION

| | |
|--------------------|--------------|
| Construction Type: | Encapsulated |
| Mounting Type: | Floor |
| Wiring Diagram: | 62 |

PACKAGING

| | |
|-----------------------|-------------|
| Ship Weight (Lbs/Kg): | 270 (123.0) |
|-----------------------|-------------|

COMPLIANCES

| | |
|---------------|---|
| UL Standard: | UL 506 |
| UL Listed: | File E79947 |
| CSA Standard: | C22.2 No. 47 |
| CSA Listed: | LR7357-32 |
| Warranty: | Acme Electric Warranty Card www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf |