

Wiha Precision Slotted/Phillips Drivers



261 Phillips Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

[SHOP](#)

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26102	000	40	1.6	2.0	.08	120	4.7	.02	10
26100	00	40	1.6	2.0	.08	120	4.7	.02	10
26101	00	75	3.0	2.0	.08	155	6.1	.02	10
26105	0	50	2.0	3.0	.12	145	5.7	.02	10
26108	0	75	3.0	3.0	.12	170	6.7	.03	10
26107	0	100	3.9	3.0	.12	195	7.6	.05	10
26109	0	150	5.9	3.0	.12	245	9.6	.06	10
26110	1	60	2.4	4.0	.16	170	6.7	.05	10
26113	1	80	3.1	4.0	.16	190	7.5	.05	10
26114	1	100	3.9	4.0	.16	210	8.2	.06	10
26115	1	150	5.9	4.0	.16	260	10.2	.07	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26092 7 Piece Precision Slotted & Phillips Set Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Slotted:	lbs.
26092	2.5 x 50mm,	.30
	2.5, 3.0, 4.0 x 100mm	
	3.0, 4.0 x 150mm	
Phillips:		
	0 x 75mm	



[SHOP](#)

26190 7 Piece Precision Slotted & Phillips Set Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Slotted:	lbs.
26190	1.5 x 40mm	.31
	2.0, 2.5 x 50mm	
	3.0 x 60mm	
Phillips:		
	00 x 40mm	
	0 x 50mm, 1 x 60mm	



[SHOP](#)

26194 4 Piece Precision Phillips Set

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.

Item No.	Phillips:	lbs.
26194	000, 00 x 40mm	.18
	0 x 50mm, 1 x 60mm	



In canvas storage pouch

[SHOP](#)

26199 8 Piece Precision Slotted/Phillips Set

Blade high alloy CVM steel, hard chrome finished.

Item No.	Slotted:	lbs.
26199	1.0, 2.0 x 40mm, 3.0 x 50mm	.55
	4.0 x 60mm	
Phillips:		
	000, 00 x 40mm, 0 x 50mm,	
	1 x 60mm	



[SHOP](#)

26192 5 Piece Precision Slotted & Phillips Set Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Slotted:	lbs.
26192	2.5, 3.0, 4.0 x 150mm	.44
Phillips:		
	0, 1 x 150mm	

