



Safety Plates PC 5050, 5060

Steel safety plates are affixed to the face of 2" x 4" members to protect utility pipes and to prevent nails from penetrating into hidden live wires (NMC cable) which may be running through notches or through the drilled holes in the stud.

- 16 Gauge Steel
- 20 Gauge Steel
- Nail Sharp Points
- Easy to Install
- Available in Boxes Or Pails
- Caution! Always Wear Eye Protection

CAT NO	UPC	SIZE	GAUGE	STD	MSTR	WT/STD	UNIT
PC 5050							
411	14100	1-1/2 x 2-3/4"	16	100	1000	7.00#	C
415	14105	1-1/2 x 2-3/4"	16	500	500	35.00#	C
41P	14116	1-1/2 x 2-3/4"	16	500(Pail)	500(Pail)	35.00#	C
PC 5060							
2516	14110	1-3/4 x 5"	16	100	100	16.00#	C
2520	14115	1-3/4 x 5"	20	100	100	10.00#	C
3516	14120	3 x 5"	16	100	100	26.80#	C

Dottie guarantees these plates to be 16 ga (.0538 to .0658) as required by some codes. Dottie makes no warranty that these plates cannot be pierced by powder actuated / gas powered nail guns.

Plate Straps PC 5150

Plate straps are nailed across studs to restrain pipe between studs; installed over utility pipes & electrical wire that pass through framing members to prevent piercing.

- 12 Gauge Steel
- 16 Gauge Steel
- Various Lengths
- Caution! Always Wear Eye Protection

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
PS129	60010	1-1/2 x 9"	50	50	16.66#	C
PS1212	60012	1-1/2 x 12"	50	50	23.50#	C
PS1218	60014	12 Gauge 1-1/2 x 18"	50	50	36.00#	C
PS1224	60016	1-1/2 x 24"	50	50	41.20#	C
PS169	60018	1-1/2 x 9"	50	50	9.14#	C
PS1612	60020	1-1/2 x 12"	50	50	15.40#	C
PS1618	60022	16 Gauge 1-1/2 x 18"	50	50	19.58#	C
PS1624	60024	1-1/2 x 24"	50	50	28.50#	C

Nail Straps PC 5070, 5080, 5090

Nail Straps are a stamped steel strap (J hook) which is nailed into studs to support tubing, pipe or E.M.T. Available in zinc or copper plated, and in copper plated with the top plastic coated.

- 12 Gauge Steel
- Copper Plated
- Zinc or Copper Plated
- Caution! Always Wear Eye Protection
- With Plastic Coating

CAT NO	UPC	SIZE	DESCRIPTION	STD	MSTR	WT/STD	UNIT
Zinc Plated - PC 5070							
D1	27655	1/2"	Pipe	100	1000	1.94#	M
D1P	27658	1/2"	Pipe	2000 (Pail)	2000 (Pail)	39.90#	M
D2	27660	3/4"	Pipe	100	1000	2.32#	M
D3	27665	1"	Pipe	100	1000	2.63#	M
D11	27670	1/2"	E.M.T.	100	1000	1.53#	M
D12	27675	3/4"	E.M.T.	100	1000	1.99#	M
D13	27680	1"	E.M.T.	100	1000	2.30#	M
Copper Plated - PC 5080							
K1	27100	1/2"	Tube	100	1000	1.60#	M
K2	27102	3/4"	Tube	100	1000	1.86#	M
K3	27104	1"	Tube	100	1000	2.36#	M
K4	27106	1-1/4"	Tube	100	1000	2.36#	M
Copper Plated w/ Plastic Coating - PC 5090							
PL10	27107	1/2"	Tube 3/8" Iron	100	1000	1.72#	M
PL20	27108	3/4"	Tube 1/2" Iron	100	1000	2.04#	M
PL30	27110	1"	Tube 3/4" Iron	50	500	1.30#	M
PL40	27112	1-1/4"	Tube 1" Iron	50	500	1.55#	M

