



Drop In Anchors PC 4500, 4310

Drop In Anchors: This steel anchor performs well in a variety of concrete strengths. Can be used in brick. Any head style screw can be used. The screw can easily be removed or loosened and retightened. Drill hole in concrete and drop anchor into hole. Place setting tool over anchor and hammer until set.

- Drop In
- Zinc Plated Steel
- Stainless Steel
- Caution! Always Wear Eye Protection

CAT NO	UPC	ANCHOR SIZE	DRILL SIZE	REQUIRED TOOL	STD	MSTR	WT/STD	UNIT
Steel Zinc Plated - PC 4500								
DA25	27600	1/4-20	3/8"	AT25	100	1000	2.00#	C
DA38	27605	3/8-16	1/2"	AT38	50	500	3.00#	C
DA50	27610	1/2-13	5/8"	AT50	50	250	6.00#	C
DA58	27615	5/8-11	7/8"	AT58	25	125	6.00#	C
DA75	27620	3/4-10	1"	AT75	10	50	4.80#	C
Stainless Steel - PC 4310								
DAS25	70260	1/4-20	3/8"	AT25	100	1000	2.00#	C
DAS38	70262	3/8-16	1/2"	AT38	50	500	3.00#	C
DAS50	70264	1/2-13	5/8"	AT50	50	250	6.00#	C
DAS58	70266	5/8-11	7/8"	AT58	25	125	6.00#	C
DAS75	70268	3/4-10	1"	AT75	10	50	4.80#	C

("AT" Tool - SOLD SEPARATELY - Must Be Used For Proper Installation)



"AT" Tool For DA Anchors PC 4510

"AT" tool must be used for proper installation. Sold separately from DA/DAS anchors

CAT NO	UPC	SIZE	ANCHOR TYPE	STD	MSTR	WT/STD	UNIT
AT25	27630	1/4"	DA25/DAS25	1	10	0.14#	Ea
AT38	27635	3/8"	DA38/DAS38	1	10	0.25#	Ea
AT50	27570	1/2"	DA50/DAS50	1	10	0.41#	Ea
AT58	27575	5/8"	DA58/DAS58	1	10	0.55#	Ea
AT75	27580	3/4"	DA75/DAS75	1	10	0.77#	Ea



Sleeve Anchors - Zinc Plated PC 4550

Sleeve Anchors: Similar to the wedge anchor. It can be used in the same materials as the wedge anchor, but can also be used in soft concretes because the compression load can be distributed over a longer length. Can be installed through the fixture. Assemble nut and washer on stud and insert into predrilled hole. Anchor is hammered into hole until the nut is seated.

- Sleeve
- Hex or Acorn Nut
- Zinc Plated
- Available In Larger Diameters & Lengths

CAT NO	UPC	SIZE	BOLT LENGTH	DRILL DIA	MIN. EMBED	STD	MSTR	WT/STD	UNIT
Acorn Nut									
SA14138	59330	1/4 x 1-3/8"	1-21/32"	1/4"	1-1/8"	100	600	2.75#	C
SA14214	59332	1/4 x 2-1/4"	2-9/16"	1/4"	1-1/8"	100	600	3.25#	C
Hex Nut									
SA516112	59334	5/16 x 1-1/2"	1-13/16"	5/16"	1-3/8"	100	600	4.25#	C
SA516212	59336	5/16 x 2-1/2"	2-11/16"	5/16"	1-1/2"	100	500	5.75#	C
SA38178	59338	3/8 x 1-7/8"	2-3/16"	3/8"	1-5/8"	50	300	3.50#	C
SA38300	59340	3/8 x 3"	3-5/16"	3/8"	1-5/8"	50	250	5.00#	C
SA12214	59342	1/2 x 2-1/4"	2-7/8"	1/2"	2-1/8"	25	150	3.50#	C
SA12300	59344	1/2 x 3"	3-3/8"	1/2"	2-1/4"	25	150	4.30#	C
SA12400	59346	1/2 x 4"	4-3/8"	1/2"	2-1/4"	25	150	5.50#	C

