



Reducing Bushings PC 5430

Reducing bushings are used with rigid /IMC conduit to reduce the size of a threaded opening to accept a smaller size conduit.

- Zinc Plated Steel
- High Strength Malleable Iron

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
R351	30500	1/2 x 3/8"	100	500	2.40#	C
R352	30505	3/4 x 1/2"	100	500	5.00#	C
R353	30510	1 x 1/2"	50	250	5.88#	C
R354	30515	1 x 3/4"	50	250	6.77#	C
R355	30520	1-1/4 x 1/2"	25	125	3.44#	C
R356	30525	1-1/4 x 3/4"	25	125	5.33#	C
R357	30530	1-1/4 x 1"	25	125	3.70#	C
R358	30535	1-1/2 x 1/2"	25	125	10.06#	C
R359	30540	1-1/2 x 3/4"	25	125	8.25#	C
R360	30545	1-1/2 x 1"	25	125	6.45#	C
R361	30550	1-1/2 x 1-1/4"	25	125	2.78#	C
R362	30555	2 x 1/2"	10	50	8.18#	C
R363	30560	2 x 3/4"	10	50	7.34#	C
R364	30565	2 x 1"	10	50	6.50#	C
R365	30570	2 x 1-1/4"	10	50	4.81#	C
R366	30575	2 x 1-1/2"	10	50	3.27#	C
R367	30576	2-1/2 x 2"	1	10	0.60#	C
R368	30577	3 x 2"	1	10	1.04#	C
R369	30578	3 x 2-1/2"	1	10	1.22#	C
R370	30579	3-1/2 x 2"	1	10	1.39#	C
R371	30580	3-1/2 x 2-1/2"	1	10	1.48#	C
R372	30581	3-1/2 x 3"	1	10	1.17#	C
R373	30582	4 x 2"	1	10	3.62#	C
R374	30583	4 x 2-1/2"	1	10	1.95#	C
R375	30584	4 x 3"	1	10	1.64#	C
R376	30585	4 x 3-1/2"	1	10	1.28#	C



Plastic Bushings PC 5670

Plastic bushings are threaded onto the end of conduit and are used to protect wires coming through the conduit.

- UL Listed
- Thermoplastic
- 105° C
- Fits Rigid Conduit

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
PB50	10100	1/2"	100	1000	0.49#	C
PB75	10105	3/4"	100	1000	0.64#	C
PB100	10110	1"	50	500	0.58#	C
PB125	10115	1-1/4"	25	250	0.44#	C
PB150	10120	1-1/2"	25	250	0.50#	C
PB200	10125	2"	25	250	0.74#	C
PB250	10130	2-1/2"	25	100	1.32#	C
PB300	10135	3"	25	100	1.55#	C
PB350	10140	3-1/2"	10	50	0.85#	C
PB400	10145	4"	10	20	0.98#	C
PB500	10150	5"	10	10	2.93#	C
PB600	10155	6"	10	10	3.85#	C



EMT Bushings PC 5675

EMT Insulating Bushings protect cables from abrasion. Use where nonmetallic low voltage cabling is installed in EMT.

- Stay-In-Place Design
- Engineered Plastic
- Color: White

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
EMTB50	81613	1/2"	100	1000	0.40#	C
EMTB75	81614	3/4"	50	500	0.25#	C
EMTB100	81615	1"	25	250	0.23#	C
EMTB125	81616	1-1/4"	25	250	0.27#	C
EMTB150	81617	1-1/2"	25	100	0.35#	C
EMTB200	81618	2"	25	100	0.55#	C
EMTB250	81619	2-1/2"	25	100	1.40#	C
EMTB300	81620	3"	25	100	1.30#	C
EMTB350	81621	3-1/2"	25	100	2.10#	C
EMTB400	81622	4"	25	100	3.20#	C

