



- UL Listed
- Die Cast Copper Free Aluminum
- With Covers
- With Neoprene Gaskets

Threaded Conduit Bodies with cover and gasket are used with rigid conduit to provide access to the interior of a conduit system. They are available as bodies only, or as bodies assembled with covers and gaskets. The flat back design allows the unit to be mounted close to the wall. They are die cast from high strength, copper free aluminum.

CAT NO	UPC		SIZE	STD	MSTR	WT/STD	UNIT
LB50CG	10722		1/2"	10	100	2.93#	C
LB75CG	10724		3/4"	10	50	4.10#	C
LB100CG	10726		1"	5	25	3.58#	C
LB125CG	10728		1-1/4"	2	10	2.96#	C
LB150CG	10730		1-1/2"	2	10	3.25#	C
LB200CG	10732	<b>LB</b>	2"	1	5	2.80#	C
LB250CG	10734		2-1/2"	1	1	5.10#	C
LB300CG	10736		3"	1	1	6.20#	C
LB350CG	10738		3-1/2"	1	1	9.54#	C
LB400CG	10740		4"	1	1	10.09#	C
LR50CG	10762		1/2"	10	100	2.98#	C
LR75CG	10764		3/4"	10	50	5.21#	C
LR100CG	10766		1"	5	25	3.62#	C
LR125CG	10768		1-1/4"	2	10	3.06#	C
LR150CG	10770		1-1/2"	2	10	3.33#	C
LR200CG	10772	<b>LR</b>	2"	1	5	2.80#	C
LR250CG	10774		2-1/2"	1	1	6.43#	C
LR300CG	10776		3"	1	1	9.60#	C
LR350CG	10778		3-1/2"	1	1	11.39#	C
LR400CG	10780		4"	1	1	12.00#	C
LL50CG	10742		1/2"	10	100	3.00#	C
LL75CG	10744		3/4"	10	50	5.17#	C
LL100CG	10746		1"	5	25	3.52#	C
LL125CG	10748		1-1/4"	2	10	2.93#	C
LL150CG	10750		1-1/2"	2	10	3.22#	C
LL200CG	10752	<b>LL</b>	2"	1	5	2.84#	C
LL250CG	10754		2-1/2"	1	1	5.26#	C
LL300CG	10756		3"	1	1	7.02#	C
LL350CG	10758		3-1/2"	1	1	10.35#	C
LL400CG	10760		4"	1	1	10.80#	C
C50CG	10702		1/2"	10	100	2.82#	C
C75CG	10704		3/4"	10	50	4.79#	C
C100CG	10706		1"	5	25	2.87#	C
C125CG	10708		1-1/4"	2	10	2.88#	C
C150CG	10710		1-1/2"	2	10	2.90#	C
C200CG	10712	<b>C</b>	2"	1	5	2.65#	C
C250CG	10714		2-1/2"	1	1	5.67#	C
C300CG	10716		3"	1	1	6.28#	C
C350CG	10718		3-1/2"	1	1	9.90#	C
C400CG	10720		4"	1	1	10.35#	C
T50CG	10782		1/2"	10	100	3.80#	C
T75CG	10784		3/4"	10	50	4.25#	C
T100CG	10786		1"	5	25	3.63#	C
T125CG	10788		1-1/4"	2	10	4.03#	C
T150CG	10790		1-1/2"	2	10	3.55#	C
T200CG	10792	<b>T</b>	2"	2	2	5.85#	C
T250CG	10794		2-1/2"	1	1	7.06#	C
T300CG	10796		3"	1	1	7.63#	C
T350CG	10798		3-1/2"	1	1	12.52#	C
T400CG	10802		4"	1	1	10.95#	C
TB50CG	81526		1/2"	10	100	3.80#	C
TB75CG	81527		3/4"	10	50	4.25#	C
TB100CG	81528	<b>TB</b>	1"	5	25	3.63#	C
TB125CG	81529		1-1/4"	2	10	4.03#	C
TB150CG	81530		1-1/2"	2	10	3.55#	C
TB200CG	81531		2"	2	2	5.85#	C
X50CG	81532		1/2"	10	100	3.80#	C
X75CG	81533		3/4"	10	50	4.25#	C
X100CG	81534	<b>X</b>	1"	5	25	3.63#	C
X125CG	81535		1-1/4"	2	10	4.03#	C
X150CG	81536		1-1/2"	2	10	3.55#	C
X200CG	81537		2"	2	2	5.85#	C

