

High Speed Steel Drills & Sets PC 6350



- Industrial Quality
- M2 High Speed Steel
- Heavy Duty Jobber Length
- Fractional Sizes

- 3 Flats on Sizes 3/16" and Larger
- Black and Gold Finish
- Caution! Always Wear Eye Protection


High speed drills are rolled forged and have a 135° split point. They are suitable for steel, steel forging, cast iron and other work materials.

CAT NO	UPC	SIZE	DECIMAL	LENGTH	STD	MSTR	WT/STD	UNIT
High Speed Drills / Heavy Duty Jobber								
HS4	29304	1/16"	.0625	1-7/8"	12	12	.030#	Ea
HS5	29305	5/64"	.0781	2"	12	12	.040#	Ea
HS6	29306	3/32"	.0938	2-1/4"	12	12	.050#	Ea
HS7	29307	7/64"	.1094	2-5/8"	12	12	.070#	Ea
HS8	29308	1/8"	.1250	2-3/4"	12	12	.090#	Ea
HS9	29309	9/64"	.1406	2-7/8"	12	12	.110#	Ea
HS10	29310	5/32"	.1562	3-1/8"	12	12	.140#	Ea
HS11	29311	11/64"	.1719	3-1/4"	12	12	.190#	Ea
HS12	29312	3/16"	.1875	3-1/2"	12	12	.240#	Ea
HS13	29313	13/64"	.2031	3-5/8"	12	12	.270#	Ea
HS14	29314	7/32"	.2188	3-3/4"	12	12	.320#	Ea
HS15	29315	15/64"	.2344	3-7/8"	12	12	.370#	Ea
HS16	29316	1/4"	.2500	4"	12	12	.440#	Ea
HS17	29317	17/64"	.2656	4-1/8"	12	12	.740#	Ea
HS18	29318	9/32"	.2812	4-1/4"	12	12	.570#	Ea
HS19	29319	19/64"	.2969	4-3/8"	12	12	.630#	Ea
HS20	29320	5/16"	.3125	4-1/2"	12	12	.740#	Ea
HS21	29321	21/64"	.3281	4-5/8"	6	6	.440#	Ea
HS22	29322	11/32"	.3438	4-3/4"	6	6	.510#	Ea
HS23	29323	23/64"	.3594	4-7/8"	6	6	.530#	Ea
HS24	29324	3/8"	.3750	5"	6	6	.640#	Ea
HS25	29325	25/64"	.3906	5-1/8"	6	6	.660#	Ea
HS26	29326	13/32"	.4062	5-1/4"	6	6	.690#	Ea
HS27	29327	27/64"	.4219	5-3/8"	6	6	.820#	Ea
HS28	29328	7/16"	.4375	5-1/2"	6	6	.890#	Ea
HS29	29329	29/64"	.4531	5-5/8"	6	6	.930#	Ea
HS30	29330	15/32"	.4688	5-3/4"	6	6	1.000#	Ea
HS31	29331	31/64"	.4844	5-7/8"	6	6	1.090#	Ea
HS32	29332	1/2"	.5000	6"	6	6	1.150#	Ea

High Speed Drill Bit Merchandiser (252D)

Our attractive counter top High Speed Drill Merchandiser has been one of the most popular selling tools in our distributors showrooms for many years. When fully stocked our display offers a wide assortment of the most popular high speed drills to satisfy the needs of every contractor. The clear acrylic lockable lid allows for easy viewing of the product with out the concern of shrinkage.

252D



High Speed Steel Drill Sets PC 6330

- Industrial Quality
- M2 High Speed Steel
- Heavy Duty Jobber Length
- Fractional Sizes

- 3 Flats on Sizes 3/16" and Larger
- Black and Gold Finish
- Caution! Always Wear Eye Protection

High speed drills are rolled forged and have a 135° split point. They are suitable for steel, steel forging, cast iron and other work materials.



CAT NO	UPC	DESCRIPTION	SIZES	STD	MSTR	WT/STD	UNIT
M213	66500	13 pc. set	1/16"-1/4" x 64th	1	10	0.710#	Ea
M221	66550	21 pc. set	1/16"-3/8" x 64th	1	10	1.580#	Ea
M229	29850	29 pc. set	1/16"-1/2" x 64th	1	10	3.100#	Ea

Dial-A-Drill PC 6340

- Industrial Quality
- M2 High Speed Steel

- Jobber Length
- Fractional Sizes

- Caution! Always Wear Eye Protection



CAT NO	UPC	DESCRIPTION	SIZES	STD	MSTR	WT/STD	UNIT
DB13K	67510	13 pc. set	1/16"-1/4" x 64th	1	10	0.320#	Ea

See new products at Ihdottie.com



TOOLS & SPECIALTY ITEMS > HIGH SPEED DRILLS & SETS > DIAL-A-DRILL