


**Insulated Long Nose Pliers**



**SHOP**

**328 Long Nose Pliers With Cutters.** Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  up to 1000 volt. Individually Tested. Drop-forged from special tool steel, cutters additionally induction hardened (approx. 60 HRC), chrome-nickel plated, mirror-polished, ergonomic comfort grip with slip guard, half-round jaws, serrated gripping surface.


Item No.	Cutting Capacity		Pkg.	wt.
	mm	Inch		
32806	160	6.3	#10	1 .32
32808	200	8.0	#8	1 .42

**Insulated Bent Nose Pliers**

Angled 40°



**SHOP**

**328 Bent Nose Pliers With Cutters.** Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  up to 1000 volt. Individually Tested.

Drop-forged from special tool steel, cutters additionally induction hardened (approx. 60 HRC), chrome-nickel plated, mirror-polished. Ergonomic comfort grip with slip guard. Half-round jaws, serrated gripping surface, nose bent 40°.


Item No.	Cutting Capacity		Pkg.	wt.
	mm	Inch		
32804	200	8.0	#8	1 .43
32807	160	6.3	#10	1 .32

**Round Nose Pliers**

 1000volt



**SHOP**


**32870 Round Nose Pliers.** Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  up to 1000 volt. Individually Tested. Drop-forged from special tool steel, individually induction hardened, chrome and nickel plated, mirror-polished. Ergonomic comfort grip with slip guard. Serrated jaws.

Item No.	Cutting Capacity		Pkg.	wt.
	mm	Inch		
32870	160	6.3	1	.34

**Insulated Long Flat Nose Pliers**



**SHOP**

**32810 Long Flat Nose Pliers.** Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  up to 1000 volt. Individually Tested. DIN ISO 5745


Extra long head. Serrated Jaws are induction hardened. Special CV tool steel forgings, Chrome finish. Two component Soft Grip handles. Use for Gripping and right-angle bending of wires and sheet metal parts.

Item No.	Cutting Capacity		Pkg.	wt.
	mm	Inch		
32810	160	6.3	1	.39

**Insulated Stripping Pliers**



**SHOP**

**32860 Stripping Pliers.** Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA,  up to 1000 volt. Individually Tested. Heavy duty forged, induction hardened cutting edges for even stripping of insulation. Drop-forged from special tool steel, chrome and nickel plated, mirror-polished. Spring and adjusting screw, for stripping up to Ø 5mm/#4 Awg.

Item No.	Stripping Capacity		Pkg.	wt.
	mm	Inch		
32860	160	6.3	#4 - #28	1 .50

**Wiha Canvas Pliers Holster**

- Canvas holster with belt clip and belt loop
- Security pliers strap
- Screwdriver holder in the front

**SHOP**

**91256 Pliers Canvas Holster**

Item No.	Size		lbs.	pkg.
	Width	Height		
91256	3.5 x	6.75	.15	1

