



Hole Saws PC 6380

Variable pitch hole saws are bi-metal construction with an M3 HSS cutting edge which is laser welded to a spring steel back. They will cut to depths of 1-3/8" and will outlast carbon steel hole saws, while the tooth design resists shock and strippage. The saws accept standard arbors and will cut stainless steel, iron, pipe, wood and plastic.

- Bi Metal
- M3 Steel RC65-66
- Shatterproof
- 4/6 Variable Pitch
- Powder Coated
- Accepts Standard Arbors
- Caution! Always Wear Eye Protection

CAT NO	UPC	DIAMETER	USE ARBOR	PIPE SIZE				WT/STD	UNIT
				TAP	ENTR.	STD	MSTR		
VP09	28400	9/16"	V24K, V34, V44			1	10	0.080#	Ea
VP10	28402	5/8"	V24K, V34, V44			1	10	0.090#	Ea
VP11	28404	11/16"	V24K, V34, V44			1	10	0.090#	Ea
VP12	28406	3/4"	V24K, V34, V44		3/8"	1	10	0.090#	Ea
VP13	28408	13/16"	V24K, V34, V44			1	10	0.110#	Ea
VP14	28410	7/8"	V24K, V34, V44	3/4"	1/2"	1	10	0.110#	Ea
VP15	28412	15/16"	V24K, V34, V44			1	10	0.130#	Ea
VP16	28414	1"	V24K, V34, V44			1	10	0.140#	Ea
VP18	28416	1-1/8"	V24K, V34, V44	1"	3/4"	1	10	0.190#	Ea
VP19	28418	1-3/16"	V24K, V34, V44			1	10	0.200#	Ea
VP20	28420	1-1/4"	V35P, V45P			1	10	0.200#	Ea
VP21	28422	1-5/16"	V35P, V45P			1	10	0.210#	Ea
VP22	28424	1-3/8"	V35P, V45P		1"	1	10	0.240#	Ea
VP24	28426	1-1/2"	V35P, V45P			1	10	0.280#	Ea
VP26	28428	1-5/8"	V35P, V45P			1	10	0.340#	Ea
VP28	28430	1-3/4"	V35P, V45P	1-1/2"	1-1/4"	1	10	0.230#	Ea
VP30	28432	1-7/8"	V35P, V45P			1	10	0.270#	Ea
VP32	28434	2"	V35P, V45P		1-1/2"	1	10	0.290#	Ea
VP34	28436	2-1/8"	V35P, V45P			1	10	0.330#	Ea
VP36	28438	2-1/4"	V35P, V45P	2"		1	10	0.360#	Ea
VP37	28440	2-5/16"	V35P, V45P			1	10	0.330#	Ea
VP38	28442	2-3/8"	V35P, V45P			1	10	0.330#	Ea
VP40	28444	2-1/2"	V45P		2"	1	10	0.450#	Ea
VP41	28446	2-9/16"	V45P			1	10	0.450#	Ea
VP48	28448	3"	V45P		2-1/2"	1	10	0.600#	Ea
VP56	28450	3-1/2"	V45P			1	10	0.620#	Ea
VP58	28452	3-5/8"	V45P		3"	1	10	0.660#	Ea
VP64	28454	4"	V45P			1	10	0.810#	Ea
VP66	28456	4-1/8"	V45P		3-1/2"	1	10	0.850#	Ea
VP70	28458	4-3/8"	V45P			1	10	0.910#	Ea
VP72	28460	4-1/2"	V45P			1	10	0.960#	Ea
VP76	28462	4-3/4"	V45P		4"	1	10	1.030#	Ea
VP80	28464	5"	V45P			1	10	1.140#	Ea
VP88	28466	5-1/2"	V45P			1	10	1.300#	Ea
VP96	28468	6"	V45P			1	10	1.530#	Ea



Arbors PC 6390

Arbors are supplied with pilot drills. Check Hole Saw to determine proper arbor.

- Interchangeable With Other Brands
- Includes Replaceable High Speed Pilot Drill
- Caution! Always Wear Eye Protection

CAT NO	UPC	SHANK	THREAD SIZE	DRILL SIZE	DRILL NUMBER	DRILL SIZE	CHUCK FITS	STD	MSTR	WT/STD	UNIT
V24K	28500	1/4" Round	1/2-20	1/4"	VPD4	1/4"	9/16" - 1-1/8"	1	1	0.130#	Ea
V34	28505	3/8" Hex	1/2-20	1/4"	VDP4S	3/8"	9/16" - 1-1/8"	1	1	0.150#	Ea
V35P	28510	3/8" Hex	5/8-18	1/4"	VPD4S	3/8"	1-1/4" - 6"	1	1	0.360#	Ea
V44	28515	7/16" Hex	1/2-20	1/4"	VPD4	1/2"	9/16" - 1-1/8"	1	1	0.160#	Ea
V45P	28525	7/16" Hex	5/8-18	1/4"	VPD4	1/2"	1-1/4" - 6"	1	1	0.500#	Ea

