



Safety Products

StarLite® Squared - Good **NEW!**

StarLite® SQUARED —providing low-cost, ultra-fashionable impact protection that meets and exceeds ANSI Z87.1+ standards. This trend-setter surpasses even the coolest eyewear styles, helping to ensure worker compliance. Economically priced to fit any budget. Incredibly light eyewear – weighing less than an ounce – that provides superior impact protection. Soft, pliable temples and a fingertip nosepiece offer long-wearing comfort for end users. Snug and comfortable fit; helps minimize slippage and provides full brow protection. Size and style is popular with both men and women. Scratch-resistant, hardcoated 100% polycarbonate lens that lasts longer than non-treated lenses.

CAT NO	DESCRIPTION	UNIT	MSTR QTY
ESTR410	Amber Temple Amber Lens	10/Box	50
ESTR420	Clear Temple Clear Lens	10/Box	50
ESTR430	Gray Temple Gray Lens	10/Box	50
ESTR440	Gray Temple Silver Mirror Lens	10/Box	50
ESTR450	Gray Temple Blue Mirror Lens	10/Box	50
ESTR410D	Amber Temple Amber Lens - Display Pack	1	10
ESTR420D	Clear Temple Clear Lens - Display Pack	1	10
ESTR430D	Gray Temple Gray Lens - Display Pack	1	10
ESTR440D	Gray Temple Silver Mirror Lens - Display Pack	1	10
ESTR450D	Gray Temple Blue Mirror Lens - Display Pack	1	10

Luminary™ - Better **NEW!**

From its lightweight frame to its contemporary design, Luminary™ has the look, fit, and feel that make it one of the lightest and brightest solutions in safety eyewear. Ultra-lightweight design – just four-fifths of an ounce – makes it easy to wear all day, every day. Patent-pending design includes unique, translucent temple insets for an electrifying new look. Elastic temples help relieve pressure behind the ears and provide superior comfort. 'Fingertip' nosepiece reduces slippage, so glasses stay on securely. Large, one-piece polycarbonate lens, with an anti-scratch coating, offers durable protection. Wrap-around design, along with an integrated browguard, ensures complete protection. Meets or exceeds ANSI Z87.1+ standards.

CAT NO	DESCRIPTION	UNIT	MSTR QTY
ELUM515	Black Temple, Clear Inset, Clear Lens	10/Box	50
ELUM525	Silver Temple, Gray Inset, Gray Lens	10/Box	50
ELUM535	Black Temple, Amber Inset, Amber Lens	10/Box	50
ELUM545	Silver Temple, Gray Inset, Silver Mirror Lens	10/Box	50
ELUM555	Black Temple, Blue Inset, Blue Mirror Lens	10/Box	50
ELUM515D	Black Temple, Clear Inset, Clear Lens - Display Pack	1	10
ELUM525D	Silver Temple, Gray Inset, Gray Lens - Display Pack	1	10
ELUM535D	Black Temple, Amber Inset, Amber Lens - Display Pack	1	10
ELUM545D	Silver Temple, Gray Inset, Silver Mirror Lens - Display Pack	1	10
ELUM555D	Black Temple, Blue Inset, Blue Mirror Lens - Display Pack	1	10

Scorpion™ - Better **NEW!**

Scorpion is exceptional-quality, cost effective eyewear offering value for you and your employees. Contemporary styling results in protective eyewear that workers want to wear. Workers put them on and keep them on...longer! Adjustable length temples and finger-tip nosepiece offer custom, flexible fit. Four-point ratchet temple fits virtually any worker...better! Frame support behind lens provides added durability yet lightweight for extreme comfort. Scratch- and impact-resistant, hardcoated lens blocks more than 99.9% of UV-A and UV-B light. Free "Scorpion's Tail" retainer helps prevent loss and damage. Meets or exceeds ANSI Z87.1+ standard.

CAT NO	DESCRIPTION	UNIT	MSTR QTY
ESCO620	Black Frame/Clear Lens - with leash	10/Box	50
ESCO630	Black Frame/Gray Lens - with leash	10/Box	50
ESCO640	Black Frame/Amber Lens - with leash	10/Box	50
ESCO650	Black Frame/Silver Mirror Lens - with leash	10/Box	50
ESCO660	Black Frame/Blue Mirror Lens - with leash	10/Box	50
ESCO620D	Black Frame/Clear Lens - with leash - Display Pack	1	10
ESCO630D	Black Frame/Gray Lens - with leash - Display Pack	1	10
ESCO640D	Black Frame/Amber Lens - with leash - Display Pack	1	10
ESCO650D	Black Frame/Silver Mirror Lens - with leash - Display Pack	1	10
ESCO660D	Black Frame/Blue Mirror Lens - with leash - Display Pack	1	10

Safety Products

4x4™ - Best **NEW!**

The ideal eyewear for workers who want high-end style and protection - at cost effective pricing. Strong, four-sided frame weighs just one ounce, providing both durable protection and comfort. Wrap-around frame supports dual polycarbonate lenses that come with an anti-scratch coating. Soft inset nosepiece helps ensure comfort and provides a snug, secure fit. Flexible temple tips relieve pressure behind the ear. Meets or exceeds ANSI Z87.1+ standards.

CAT NO	DESCRIPTION	UNIT	MSTR QTY
E4X4700	Black Frame/Clear Lens	10/Box	50
E4X4715	Black Frame/Grey Lens	10/Box	50
E4X4730	Black Frame/Amber Lens	10/Box	50
E4X4745	Black Frame/Clear Lens	10/Box	50
E4X4760	Black Frame/Blue Mirror Lens	10/box	50
E4X4700D	Black Frame/Clear Lens - Display Pack	1	10
E4X4715D	Black Frame/Grey Lens - Display Pack	1	10
E4X4730D	Black Frame/Amber Lens - Display Pack	1	10
E4X4745D	Black Frame/Clear Lens - Display Pack	1	10
E4X4760D	Black Frame/Blue Mirror Lens - Display Pack	1	10

4x4™ Polarized - Very Best **NEW!**

CAT NO	DESCRIPTION	UNIT	MSTR QTY
E4X4775	Black Frame/Black Temple Tips/Gray Polarized Lens - Display Pack	1	10
E4X4775D	Black Frame/Black Temple Tips/Gray Polarized Lens - Display Pack	1	10

Cover2™ - Over-the-Glasses Design **NEW!**

A revolutionary over-the-glasses design, Cover2 offers workers a compact, modern style that's significantly more attractive than traditional OTG products. One-piece polycarbonate lens offers a broad, unobstructed view of the workplace. Flexible temple tips work extremely well with prescription glasses, while minimizing pinching behind the head. Lightweight design, with adjustable-length temples, offers ultimate comfort with a custom fit. A cost-effective OTG solution that won't break the bank.

CAT NO	DESCRIPTION	UNIT	MSTR QTY
ECOV810	Black Temples/Clear Lens	1	10/Box
ECOV820	Black Temples/Gray Lens	1	10/Box

Wheelz™ - Safety Goggles **NEW!**

Wheelz™ Goggles Provide Maximum Protection Against Dirt and Debris. Lightweight, compact frame is more comfortable than traditional goggles, which tend to be big and bulky. Frame is made of a soft, flexible material, providing additional comfort for long days on the job site. Whirlwind ventilation system minimizes fogging by circulating air through the optical chamber. Elastic head strap can easily be adjusted to ensure a safe, snug fit – regardless of the worker's head size. Available in 3.0 and 5.0 IR Filter versions.

CAT NO	DESCRIPTION	UNIT	MSTR QTY
EWHE925	Clear Frame/Clear Lens	1	10/Box
EWHE935	Black Frame/Gray Lens	1	10/Box

TruAir™ - Disposable Respirator - Better and Best **NEW!**

TruAir N95 particulate respirators offer 95% filtration against aerosols free of oils below PEL. Economically priced to fit any budget. Widely accepted design that encourages compliance. Large, molded shell that helps to reduce breathing resistance, minimizing end-user fatigue. Non-latex, elastic head straps, plus an adjustable nosepiece, provide a safe, secure fit. Available with an exhalation vent that reduces hot air buildup; makes breathing easier.

CAT NO	DESCRIPTION	UNIT	MSTR QTY
MSK20	N95 Particulate Respirator 95% filtration against aerosols free of oils below PEL.		20/Box
MSK10	N95 Particulate Respirator with Vent 95% filtration against aerosols free of oils below PEL.		10/Box

Dust Mask

**CAUTION:** Do Not Use As Protection From; Asbestos, Silica or Cotton Dust, Toxic Dust, Fumes, Mists, Gas or Vapor. **NOT TO BE USED IN SPRAY PAINT OPERATIONS!**

CAT NO	DESCRIPTION	UNIT	MSTR QTY
MSK50	General Purpose Dust Mask	50	500/Box
MSK55	General Purpose Dust Mask (5 pack)	12 packs	24 packs

Ear Plugs - Better and Best

Tested by an independent, NVLAP accredited laboratory – 31 db NRR – one of the highest rated earplugs available!. Non-allergenic polyurethane formula is extraordinarily soft and comfortable. Self adjusting design exerts very little pressure on the ear canal.

CAT NO	DESCRIPTION	UNIT	MSTR QTY
MLE100	Corded, Tapered, Blue Polyurethane Earplugs <b>NEW!</b>	100 Pair	100 Pair
MLE200	Tapered, Blue Polyurethane Earplugs	200 Pair	200 Pair



Display Packaging



Merchandiser EM10

