



Carbide Tip Masonry Drill Bits PC 6320

Masonry drills have tungsten carbide tips and are suitable for brick, concrete, tile, slate and cinder block.

- Tungsten Carbide
- Tempered Body For Long Life
- Slow Spiral
- Suitable For Rotary or Percussion
- Black Oxide Coated
- One Per Display Pouch
- Caution! Always Wear Eye Protection

| CAT NO | UPC | SIZE | SHANK | STD | MSTR | WT/STD | UNIT |
|--------|-------|-----------|-------|-----|------|--------|------|
| MD1 | 30205 | 3/16 x 4" | 3/16" | 1 | 10 | 0.030# | Ea |
| MD2 | 30210 | 1/4 x 4" | 1/4" | 1 | 10 | 0.040# | Ea |
| MD2L | 30300 | 1/4 x 6" | 1/4" | 1 | 5 | 0.070# | Ea |
| MD2XL | 30302 | 1/4 x 12" | 1/4" | 1 | 5 | 0.150# | Ea |
| MD3 | 30215 | 5/16 x 4" | 1/4" | 1 | 10 | 0.060# | Ea |
| MD4 | 30220 | 3/8 x 4" | 1/4" | 1 | 10 | 0.070# | Ea |
| MD4L | 30304 | 3/8 x 6" | 1/4" | 1 | 5 | 0.130# | Ea |
| MD4XL | 30306 | 3/8 x 12" | 3/8" | 1 | 5 | 0.290# | Ea |
| MD5 | 30225 | 7/16 x 4" | 1/4" | 1 | 5 | 0.100# | Ea |
| MD6 | 30230 | 1/2 x 4" | 1/4" | 1 | 5 | 0.110# | Ea |
| MD6L | 30308 | 1/2 x 6" | 1/4" | 1 | 5 | 0.210# | Ea |
| MD6XL | 30310 | 1/2 x 12" | 3/8" | 1 | 5 | 0.450# | Ea |
| MD7L | 30312 | 5/8 x 6" | 3/8" | 1 | 5 | 0.290# | Ea |
| MD7XL | 30314 | 5/8 x 12" | 3/8" | 1 | 1 | 0.580# | Ea |
| MD8L | 30316 | 3/4 x 6" | 1/2" | 1 | 1 | 0.440# | Ea |
| MD8XL | 30318 | 3/4 x 12" | 1/2" | 1 | 1 | 0.920# | Ea |
| MD9L | 30320 | 7/8 x 6" | 1/2" | 1 | 1 | 0.560# | Ea |
| MD10L | 30322 | 1 x 6" | 1/2" | 1 | 1 | 0.710# | Ea |



SDS 4 Plus Rotary Hammer Drill Bits PC 4580

This fast, tough carbide tip provides long life, easy centering, and fast drilling through all aggregates, concrete, masonry, brick, stone and even rebar! A dynamic chisel-shaped drill head ensures swift penetration and feeds the debris simultaneously to the flute section. The 3 fluted, spacious KVS-spiral removes the debris rapidly from the bore hole, saving the operator both time and money.

- Cuts Through Rebar
- Easy Centering
- Special Flute Design
- Conforms To ANSI Standards
- Special Tungsten Carbide Tip
- Caution! Always Wear Eye Protection

| CAT NO | UPC | SIZE | DRILLING DEPTH | STD | MSTR | WT/STD | UNIT |
|-----------|-------|---------------|----------------|-----|------|--------|------|
| SDS36412 | 12200 | 3/16 x 4-1/2" | 2" | 1 | 6 | 0.082# | Ea |
| SDS36614 | 12201 | 3/16 x 6-1/4" | 4" | 1 | 6 | 0.088# | Ea |
| SDS36814 | 12202 | 3/16 x 8-1/4" | 6" | 1 | 6 | 0.100# | Ea |
| SDS3610 | 12203 | 3/16 x 10" | 8" | 1 | 6 | 0.130# | Ea |
| SDS3612 | 12204 | 3/16 x 12" | 10" | 1 | 6 | 0.150# | Ea |
| SDS732412 | 12205 | 7/32 x 4-1/2" | 2" | 1 | 6 | 0.100# | Ea |
| SDS732614 | 12206 | 7/32 x 6-1/4" | 4" | 1 | 6 | 0.120# | Ea |
| SDS732814 | 12207 | 7/32 x 8-1/4" | 6" | 1 | 6 | 0.130# | Ea |
| SDS14412 | 12208 | 1/4 x 4-1/2" | 2" | 1 | 6 | 0.100# | Ea |
| SDS14614 | 12209 | 1/4 x 6-1/4" | 4" | 1 | 6 | 0.106# | Ea |
| SDS14814 | 12210 | 1/4 x 8-1/4" | 6" | 1 | 6 | 0.136# | Ea |
| SDS1411 | 12211 | 1/4 x 11" | 9" | 1 | 6 | 0.160# | Ea |
| SDS1414 | 12212 | 1/4 x 14" | 12" | 1 | 6 | 0.190# | Ea |
| SDS516614 | 12213 | 5/16 x 6-1/4" | 4" | 1 | 6 | 0.126# | Ea |
| SDS516814 | 12214 | 5/16 x 8-1/4" | 6" | 1 | 6 | 0.150# | Ea |
| SDS38614 | 12215 | 3/8 x 6-1/4" | 4" | 1 | 6 | 0.156# | Ea |
| SDS38814 | 12216 | 3/8 x 8-1/4" | 6" | 1 | 6 | 0.192# | Ea |
| SDS381014 | 12217 | 3/8 x 10-1/4" | 8" | 1 | 6 | 0.230# | Ea |
| SDS381214 | 12218 | 3/8 x 12-1/4" | 10" | 1 | 6 | 0.294# | Ea |
| SDS3818 | 12219 | 3/8 x 18" | 16" | 1 | 6 | 0.500# | Ea |
| SDS12614 | 12220 | 1/2 x 6-1/4" | 4" | 1 | 6 | 0.194# | Ea |
| SDS121014 | 12221 | 1/2 x 10-1/4" | 8" | 1 | 6 | 0.276# | Ea |
| SDS121214 | 12222 | 1/2 x 12-1/4" | 10" | 1 | 6 | 0.406# | Ea |
| SDS1218 | 12223 | 1/2 x 18" | 16" | 1 | 6 | 0.700# | Ea |
| SDS58614 | 12224 | 5/8 x 6-1/4" | 4" | 1 | 6 | 0.220# | Ea |
| SDS588 | 12225 | 5/8 x 8" | 6" | 1 | 6 | 0.280# | Ea |
| SDS5812 | 12226 | 5/8 x 12" | 10" | 1 | 6 | 0.500# | Ea |
| SDS5818 | 12227 | 5/8 x 18" | 16" | 1 | 6 | 0.800# | Ea |
| SDS349 | 12228 | 3/4 x 9" | 6" | 1 | 6 | 0.466# | Ea |
| SDS789 | 12229 | 7/8 x 9" | 6" | 1 | 6 | 0.540# | Ea |

