




Slotted Hex Washer Head Sheet Metal Screws Zinc Plated - PC 4000

Hex washer head sheet metal screws will tap their own mating threads when driven into preformed holes in metal. Length is determined from the base of the fastener head.

- Sheet Metal Screws
- Hex Washer Head
- Slotted
- Zinc Plated Steel
- Invincibox™ Up To 2"

CAT NO	UPC	SIZE	HEX SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
HWSMS612	56500	6 x 1/2	1/4"	100	500	4000	0.25#	C
HWSMS634	56502	6 x 3/4	1/4"	100	500	4000	0.30#	C
HWSMS61	56504	#6 6 x 1	1/4"	100	500	4000	0.38#	C
HWSMS6114	56506	6 x 1-1/4	1/4"	100	500	4000	0.45#	C
HWSMS6112	56508	6 x 1-1/2	1/4"	100	500	3000	0.62#	C
HWSMS812	56550	8 x 1/2	1/4"	100	500	4000	0.33#	C
HWSMS834	56552	8 x 3/4	1/4"	100	500	4000	0.43#	C
HWSMS81	56554	8 x 1	1/4"	100	500	4000	0.53#	C
HWSMS8114	56556	#8 8 x 1-1/4	1/4"	100	500	4000	0.69#	C
HWSMS8112	56558	8 x 1-1/2	1/4"	100	500	3000	0.73#	C
HWSMS82	56560	8 x 2	1/4"	100	500	3000	0.92#	C
HWSMS8212	56562	8 x 2-1/2	1/4"	100		1000	1.30#	C
HWSMS83	56564	8 x 3	1/4"	100		1000	1.34#	C
HWSMS1012	56600	10 x 1/2	5/16"	100	500	4000	0.46#	C
HWSMS1034	56602	10 x 3/4	5/16"	100	500	4000	0.57#	C
HWSMS101	56604	10 x 1	5/16"	100	500	4000	0.73#	C
HWSMS10114	56606	#10 10 x 1-1/4	5/16"	100	500	3000	0.84#	C
HWSMS10112	56608	10 x 1-1/2	5/16"	100	500	3000	0.96#	C
HWSMS102	56610	10 x 2	5/16"	50	250	1500	0.61#	C
HWSMS10212	56612	10 x 2-1/2	5/16"	100		1000	1.44#	C
HWSMS103	56614	10 x 3	5/16"	100		1000	1.81#	C
HWSMS1234	56650	12 x 3/4	5/16"	100	500	4000	0.85#	C
HWSMS121	56652	12 x 1	5/16"	100	500	3000	0.98#	C
HWSMS12114	56654	12 x 1-1/4	5/16"	100	500	3000	1.14#	C
HWSMS12112	56656	#12 12 x 1-1/2	5/16"	100	500	3000	1.31#	C
HWSMS122	56658	12 x 2	5/16"	50	250	1500	0.81#	C
HWSMS12212	56660	12 x 2-1/2	5/16"	100		1000	1.98#	C
HWSMS123	56662	12 x 3	5/16"	100		1000	2.33#	C
HWSMST834	17267	#8 Tuff Pack	8 x 3/4	1/4"	500	3000	2.21#	C
HWSMST81	17268	 8 x 1	1/4"	500		3000	2.71#	C
HWSMST1034	17269	10 x 3/4	5/16"	500		3000	3.10#	C
HWSMST101	17270	#10 Tuff Pack	10 x 1	5/16"	500	3000	3.59#	C



Pan Head Phillips Framers Screws Black Oxide - PC 4260

Phillips pan head framer screws are ideal for light duty aluminum and steel metal to metal applications. Will penetrate through 20 gauge steel studs. Length is determined from base of the fastener head. Black oxide finish.

- Pan Head
- Phillips
- Black Oxide
- Metal Piercing
- Invincibox™ Up To 2"

CAT NO	UPC	SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
F6716	67160	6 x 7/16	100	500	4000	0.22#	C
FT6716	16390	#6 Tuff Pack	6 x 7/16	500	3000	1.10#	C

