



## Duct Tape PC 5380

Duct Tape will adhere to all types of surfaces. The polyethylene coated cloth construction provides superior mechanical strength and conforms well to irregular surfaces. It is excellent for bundling, patching and sealing. It tears straight and is curl resistant.

- 2" x 60 Yards
- Temperature Rating 200° F
- 9 Mil - Cloth Backing
- Individual Cello Wrap
- Colors Available Upon Request

CAT NO	UPC	DIMENSIONS	COLOR	STD	MSTR	WT/STD	UNIT
DT260	28100	2" x 60 yds	Silver	12	24	19.50#	Ea
DT260Red	81064	2" x 60 yds	Red	12	24	19.50#	Ea



## Pipe Wrap - PVC PC 5420


Pipe Wrap is a polyvinyl chloride film coated with a rubber resin adhesive which protects pipe, joints, conduit and couplings for overhead or direct burial applications. It is corrosion and puncture resistant.

- 1", 2" & 4" Widths
- UPC Approved
- 10 Mil and 20 Mil
- Abrasion Resistant
- Provides Electrical Protection



Plumbing Code

CAT NO	UPC	DIMENSIONS	MIL	STD	MSTR	WT/STD	UNIT
110	28110	1" x 100'	10 Mil	48	48	29.28#	Ea
210	28140	2" x 100'	10 Mil	24	24	28.80#	Ea
410	28142	4" x 100'	10 Mil	12	12	27.60#	Ea
220	28145	2" x 100'	20 Mil	24	24	53.52#	Ea



## Masking Tape PC 5410

Masking Tape is a general purpose tape which is tan in color and is supplied for indoor applications. The outdoor version, 200-MT, is blue in color and UV resistant. It has a low tack and is easily removed where application and cleanup are several days apart.

- 3/4", 1", 1-1/2" & 2"
- 60 Yard Rolls

CAT NO	UPC	DIMENSIONS	STD	MSTR	WT/STD	UNIT
<b>Masking Tape</b>						
75MT	30005	3/4" x 60 yds	48	48	11.52#	Ea
100MT	30010	1" x 60 yds	36	36	10.80#	Ea
150MT	30015	1-1/2" x 60 yds	24	24	12.00#	Ea
200MT	30020	2" x 60 yds	24	24	15.12#	Ea

### Outdoor Masking Tape (Blue)

200-MT Blue	28143	2" x 60 yds	24	24	16.68#	Ea
-------------	-------	-------------	----	----	--------	----



## Barricade Tape PC 5320

Barricade Tape is used for marking physical hazards or off limit areas. Other legends, colors on request. Meets OSHA 1910.144 for marking physical hazards.

- Reusable Polyethylene
- Continuous Warning
- 3" Wide x 1,000 or 300 Ft.
- Custom Legends Available

CAT NO	UPC	LEGEND	COLOR	STD	MSTR	WT/STD	UNIT
<b>3" x 1,000 Ft.</b>							
BT5	16330	Caution Caution Caution	Yellow	1	12	4.86#	Ea
BT8	16332	Caution Do Not Enter	Yellow	1	12	4.86#	Ea
BT12	16335	Caution High Voltage	Yellow	1	12	4.86#	Ea
BT13	16334	Caution Keep Out	Yellow	1	12	4.86#	Ea
BT19	16336	Caution Open Trench	Yellow	1	12	4.86#	Ea
BT31	16338	Alternating Stripes	Black/Yellow	1	12	4.86#	Ea
BT32	16339	Alternating Stripes	Red/White	1	12	4.86#	Ea
BT49	16387	Danger Keep Out	Red	1	12	4.86#	Ea

### 3" x 300 Ft.

BT5X3	16331	Caution Caution Caution	Yellow	1	12	1.36#	Ea
BT8X3	16333	Caution Do Not Enter	Yellow	1	12	1.36#	Ea
BT13X3	16337	Caution Keep Out	Yellow	1	12	1.36#	Ea

