

Staples PC 5020, 5025



- 12 Gauge Steel
- Rust Inhibitor
- Finger Friendly
- Boxed or in Pails
- Caution! Always Wear Eye Protection

Staples are used to attach NMC (non metallic cable) or BX (armored) cable to wooden studs. The RX Series is used for Romex® and the BX Series is used for Romex® and BX. The SEU staple is used for service entrance cable and is available in 100 pack. For electro galvanized specify G (i.e.; RXG50, BXG or SEU63G). Plastic Insulated staples are used for coaxial cable, bell wire, thermostat wire, telephone wire and Romex®.





CAT NO	UPC	CABLE SIZE	SIZE (W X L)	GAUGE	STD	MSTR	WT/STD	UNIT
1/2" - 2 Conductor (#12 & #14) Romex® and other type NM Cable - PC 5020								
RX501	30710	14-2, 12-2	1/2 x 1"	12 GA	100	5000	0.57#	M
RX505	30715	14-2, 12-2	1/2 x 1"	12 GA	500	5000	2.75#	M
RX50B	30720	14-2, 12-2	1/2 x 1"	12 GA	5000	5000	28.12#	M
RX503P	30725	14-2, 12-2	1/2 x 1"	12 GA	10000	10000(Pail)	56.60#	M
9/16" - 3 Conductor (#10, #12 & #14) Romex®, BX, MC and other Cable - PC 5020								
BX1001	27010	14-3, 12-3, 10-3	9/16 x 1-3/16"	12 GA	100	5000	0.69#	M
BX1005	27015	14-3, 12-3, 10-3	9/16 x 1-3/16"	12 GA	500	5000	3.38#	M
BX100B	27020	14-3, 12-3, 10-3	9/16 x 1-3/16"	12 GA	5000	5000	34.50#	M
BX3P	27025	14-3, 12-3, 10-3	9/16 x 1-3/16"	12 GA	7500	7500(Pail)	51.64#	M
SEU - PC 5025								
SEU63	27130	6/3 SEU Cable	13/16 x 1-3/8"	12 GA	100	1000	1.09#	M
SEU43	27135	4/3 & 2/3 SEU Cable	1-1/8 x 1-1/2"	12 GA	100	1000	1.30#	M

Staples - Electro Galvanized PC 5022, 5024



CAT NO	UPC	CABLE SIZE	SIZE (W X L)	GAUGE	STD	MSTR	WT/STD	UNIT
1/2" - 2 Conductor (#12 & #14) Romex® and other type NM Cable - PC 5022								
RXG501	10530	14-2, 12-2, 10-2	1/2 x 1"	12 GA	100	5000	0.60#	M
RXG505	10531	14-2, 12-2, 10-2	1/2 x 1"	12 GA	500	5000	2.85#	M
RXG503P	10532	14-2, 12-2, 10-2	1/2 x 1"	12 GA	10000	10000(Pail)	59.50#	M
9/16" - 3 Conductor (#10, #12 & #14) Romex®, BX, MC and other Cable - PC 5022								
BXG1001	10533	14-3, 12-3, 10-3	9/16 x 1-3/16"	12 GA	100	5000	0.70#	M
BXG1005	10534	14-3, 12-3, 10-3	9/16 x 1-3/16"	12 GA	500	5000	3.50#	M
BXG3P	10535	14-3, 12-3, 10-3	9/16 x 1-3/16"	12 GA	7500	7500(Pail)	52.50#	M
SEU - PC 5024								
SEU63G	27131	6/3 SEU Cable	13/16 x 1-3/8"	12 GA	100	1000	1.09#	M
SEU43G	27136	4/3 & 2/3 SEU Cable	1-1/8 x 1-1/2"	12 GA	100	1000	1.32#	M

Staples - Plastic Insulated PC 5026

CAT NO	UPC	CABLE SIZE	SIZE	COLOR	STD	MSTR	WT/STD	UNIT
1/2" - 2 Conductor (#12 & #14) Romex® and other type NM Cable								
PLX501	27140	14-2, 12-2	1/2"	White	100	5000	0.57#	M
PLX505	27142	14-2, 12-2	1/2"	White	500	5000	2.44#	M
PLX50P	27144	14-2, 12-2	1/2"	White	4000	4000(Pail)	22.80#	M
9/16" - 3 Conductor (#10, #12 & #14) Romex®, BX, MC and other Cable								
PLX751	27146	14-3, 12-3, 10-3	3/4"	White	100	5000	0.62#	M
PLX755	27148	14-3, 12-3, 10-3	3/4"	White	500	5000	2.53#	M
PLX75P	27150	14-3, 12-3, 10-3	3/4"	White	3000	3000(Pail)	15.60#	M
Co-Axial Straps (Use Co-Axial RG-6 & RG-59U)								
PLX250W	10523	Tuff Pack 	1/4"	White	500	3000	1.16#	M
PLX250B	10539	Tuff Pack 	1/4"	Black(UV)	500	3000	1.16#	M
Bell, Telephone & Thermostat Wire Straps								
PLX18W	10540	Tuff Pack 	1/4 x 1/8"	White	500	3000	1.08#	M
PLX18B	10541	Tuff Pack 	1/4 x 1/8"	Black(UV)	500	3000	1.08#	M