



Carbide Tip Masonry Drill Bits PC 6320

Masonry drills have tungsten carbide tips and are suitable for brick, concrete, tile, slate and cinder block.

- Tungsten Carbide
- Tempered Body For Long Life
- Slow Spiral
- Suitable For Rotary or Percussion
- Black Oxide Coated
- One Per Display Pouch
- Caution! Always Wear Eye Protection

CAT NO	UPC	SIZE	SHANK	STD	MSTR	WT/STD	UNIT
MD1	30205	3/16 x 4"	3/16"	1	10	0.030#	Ea
MD2	30210	1/4 x 4"	1/4"	1	10	0.040#	Ea
MD2L	30300	1/4 x 6"	1/4"	1	5	0.070#	Ea
MD2XL	30302	1/4 x 12"	1/4"	1	5	0.150#	Ea
MD3	30215	5/16 x 4"	1/4"	1	10	0.060#	Ea
MD4	30220	3/8 x 4"	1/4"	1	10	0.070#	Ea
MD4L	30304	3/8 x 6"	1/4"	1	5	0.130#	Ea
MD4XL	30306	3/8 x 12"	3/8"	1	5	0.290#	Ea
MD5	30225	7/16 x 4"	1/4"	1	5	0.100#	Ea
MD6	30230	1/2 x 4"	1/4"	1	5	0.110#	Ea
MD6L	30308	1/2 x 6"	1/4"	1	5	0.210#	Ea
MD6XL	30310	1/2 x 12"	3/8"	1	5	0.450#	Ea
MD7L	30312	5/8 x 6"	3/8"	1	5	0.290#	Ea
MD7XL	30314	5/8 x 12"	3/8"	1	1	0.580#	Ea
MD8L	30316	3/4 x 6"	1/2"	1	1	0.440#	Ea
MD8XL	30318	3/4 x 12"	1/2"	1	1	0.920#	Ea
MD9L	30320	7/8 x 6"	1/2"	1	1	0.560#	Ea
MD10L	30322	1 x 6"	1/2"	1	1	0.710#	Ea



SDS 4 Plus Rotary Hammer Drill Bits PC 4580

This fast, tough carbide tip provides long life, easy centering, and fast drilling through all aggregates, concrete, masonry, brick, stone and even rebar! A dynamic chisel-shaped drill head ensures swift penetration and feeds the debris simultaneously to the flute section. The 3 fluted, spacious KVS-spiral removes the debris rapidly from the bore hole, saving the operator both time and money.

- Cuts Through Rebar
- Easy Centering
- Special Flute Design
- Conforms To ANSI Standards
- Special Tungsten Carbide Tip
- Caution! Always Wear Eye Protection

CAT NO	UPC	SIZE	DRILLING DEPTH	STD	MSTR	WT/STD	UNIT
SDS36412	12200	3/16 x 4-1/2"	2"	1	6	0.082#	Ea
SDS36614	12201	3/16 x 6-1/4"	4"	1	6	0.088#	Ea
SDS36814	12202	3/16 x 8-1/4"	6"	1	6	0.100#	Ea
SDS3610	12203	3/16 x 10"	8"	1	6	0.130#	Ea
SDS3612	12204	3/16 x 12"	10"	1	6	0.150#	Ea
SDS732412	12205	7/32 x 4-1/2"	2"	1	6	0.100#	Ea
SDS732614	12206	7/32 x 6-1/4"	4"	1	6	0.120#	Ea
SDS732814	12207	7/32 x 8-1/4"	6"	1	6	0.130#	Ea
SDS14412	12208	1/4 x 4-1/2"	2"	1	6	0.100#	Ea
SDS14614	12209	1/4 x 6-1/4"	4"	1	6	0.106#	Ea
SDS14814	12210	1/4 x 8-1/4"	6"	1	6	0.136#	Ea
SDS1411	12211	1/4 x 11"	9"	1	6	0.160#	Ea
SDS1414	12212	1/4 x 14"	12"	1	6	0.190#	Ea
SDS516614	12213	5/16 x 6-1/4"	4"	1	6	0.126#	Ea
SDS516814	12214	5/16 x 8-1/4"	6"	1	6	0.150#	Ea
SDS38614	12215	3/8 x 6-1/4"	4"	1	6	0.156#	Ea
SDS38814	12216	3/8 x 8-1/4"	6"	1	6	0.192#	Ea
SDS381014	12217	3/8 x 10-1/4"	8"	1	6	0.230#	Ea
SDS381214	12218	3/8 x 12-1/4"	10"	1	6	0.294#	Ea
SDS3818	12219	3/8 x 18"	16"	1	6	0.500#	Ea
SDS12614	12220	1/2 x 6-1/4"	4"	1	6	0.194#	Ea
SDS121014	12221	1/2 x 10-1/4"	8"	1	6	0.276#	Ea
SDS121214	12222	1/2 x 12-1/4"	10"	1	6	0.406#	Ea
SDS1218	12223	1/2 x 18"	16"	1	6	0.700#	Ea
SDS58614	12224	5/8 x 6-1/4"	4"	1	6	0.220#	Ea
SDS588	12225	5/8 x 8"	6"	1	6	0.280#	Ea
SDS5812	12226	5/8 x 12"	10"	1	6	0.500#	Ea
SDS5818	12227	5/8 x 18"	16"	1	6	0.800#	Ea
SDS349	12228	3/4 x 9"	6"	1	6	0.466#	Ea
SDS789	12229	7/8 x 9"	6"	1	6	0.540#	Ea

