

Jack Chain • Bright Galvanized
PC 5000



Jack chain is used for suspending fixtures.

- Jack Chain
- Steel
- Used For Suspending Fixtures

CAT NO	UPC	GAUGE	DIAMETER	WORK LOAD	BREAK LOAD	SIZE	STD	MSTR	WT/STD	UNIT
CH1010	27475	#10	.135	43 lbs	170 lbs	#10	100'	500'	14.95#	C
CH10P (Pail)	27405	#10	.135	43 lbs	170 lbs	#10	300'	300'	43.90#	C
CH1212	27485	#12	.105	29 lbs	115 lbs	#12	100'	1000'	8.78#	C
CH12P (Pail)	27415	#12	.105	29 lbs	115 lbs	#12	300'	300'	27.00#	C
CH1414	27495	#14	.080	16 lbs	65 lbs	#14	100'	1000'	5.18#	C
CH1616	27490	#16	.080	10 lbs	40 lbs	#16	100'	1000'	3.00#	C



Double Loop
Jack Chain - PC 5010

Double loop is a locked link chain with higher load ratings than jack chain. Because the links cannot be opened it requires the use of the S hook.


- Double Loop Jack Chain
- Locked Link
- Steel

CAT NO	UPC	GAUGE	DIAMETER	WORK LOAD	BREAK LOAD	SIZE	STD	MSTR	WT/STD	UNIT
DL2/0	28055	#10	.135	255 lbs	1020 lbs	#2/0	100'	500'	17.43#	C
DL1/0	28050	#11	.120	200 lbs	800 lbs	#1/0	100'	500'	13.32#	C
DL1	28060	#12	.105	155 lbs	620 lbs	#1	100'	500'	10.22#	C
DL2	28065	#13	.091	115 lbs	460 lbs	#2	100'	500'	8.25#	C
DL3	28070	#14	.080	90 lbs	360 lbs	#3	100'	500'	6.40#	C

WORKING LOAD LIMIT designates the maximum stress in pounds which should ever be applied to chain. This refers also to chain in the best condition, when new and when the load is applied uniformly to a straight, untwisted length of chain.

BREAK TEST LOAD is the maximum load in pounds at which new chain has been found by experience to break, under tests in which the load is applied in direct tension to a straight length of chain with a uniform rate of speed on a standard chain testing machine.

STANDARD FINISH: BRIGHT GALV Our chain is made from quality, silver bright, galvanized steel wire. Tests have shown chain made from galvanized wire to be superior in rust resistance to chain which is zinc plated after forming.



U Bolt
PC 4870

U Bolts are generally used to support conduit from strut. Provided with hex nuts and plate. Pipe sizes are inside diameters.

- U Bolts
- Low Carbon Steel
- NC Rolled Threads
- Zinc Plated
- Sizes Thru 4" Include Hex Nuts & Plate

CAT NO	UPC	FOR PIPE	THREAD DIAMETER (A)	INSIDE DIAMETER (C)	INSIDE LENGTH (B)	THREAD LENGTH (T)	STD	MSTR	WT/STD	UNIT
U50	17910	1/2"	1/4"	1"	1-3/4"	1"	25	25	2.22#	C
U75	17915	3/4"	1/4"	1-1/8"	2"	1"	25	25	2.42#	C
U100	17920	1"	1/4"	1-1/2"	2-3/4"	1-3/8"	25	25	2.91#	C
U125	17925	1-1/4"	5/16"	1-3/4"	2-11/16"	1-1/8"	25	25	4.59#	C
U150	17930	1 1/2"	5/16"	2"	2-11/16"	1-1/8"	25	25	4.84#	C
U200	17935	2"	5/16"	2-1/2"	3-3/16"	1-1/8"	25	250	5.54#	C
U250	17940	2-1/2"	3/8"	3"	3-5/8"	1-1/4"	10	10	3.71#	C
U300	17945	3"	3/8"	3-1/2"	4-1/2"	1-5/8"	10	10	4.17#	C
U350	17950	3-1/2"	1/2"	4"	5-1/2"	1-1/2"	10	10	9.61#	C
U400	17955	4"	1/2"	4-1/2"	6-1/2"	2-1/4"	10	10	10.16#	C

