

Wall Plate Slotted Oval Head Screws Chip Resistant - PC 4040



- Wall Plate Screws
- Slotted
- Oval Head
- Painted or Plated
- Chip Resistant

Oval Head Wall Plate screws are available in a variety of painted finishes such as Ivory, White, Brown and Almond. They are also available in tamperproof stainless steel or slotted stainless steel, nylon and brass plated. Selected items in lengths of 5/16", 1/2", 3/4" and 1".

CAT NO	UPC	SIZE	COLOR	STD	SLEEVE	MSTR	WT/STD	UNIT
413BRN	15892	6-32 x 5/16	Brown	100	500	4000	0.18#	C
413IV	15894	6-32 x 5/16	Ivory	100	500	4000	0.18#	C
413WHT	15896	6-32 x 5/16	White	100	500	4000	0.18#	C
413ALD	15898	6-32 x 5/16	Almond	100	500	4000	0.18#	C
414BRS	15900	6-32 x 1/2	Brass	100	500	4000	0.24#	C
414BRN	15905	6-32 x 1/2	Brown	100	500	4000	0.24#	C
414IV	15910	6-32 x 1/2	Ivory	100	500	4000	0.24#	C
414NY	15913	6-32 x 1/2	Nylon	100	500	4000	0.24#	C
414SS	15915	6-32 x 1/2	Stainless	100	500	4000	0.24#	C
414TP	15917	6-32 x 1/2	Tamper Proof	100	500	4000	0.24#	C
414WHT	15920	6-32 x 1/2	White	100	500	4000	0.24#	C
414ALD	15922	6-32 x 1/2	Almond	100	500	4000	0.24#	C
415IV	15925	6-32 x 3/4	Ivory	50	250	2000	0.16#	C
415BRN	15930	6-32 x 3/4	Brown	50	250	2000	0.16#	C
415WHT	15935	6-32 x 3/4	White	50	250	2000	0.16#	C
415ALD	15937	6-32 x 3/4	Almond	50	250	2000	0.16#	C
416IV	15940	6-32 x 1	Ivory	50	250	2000	0.20#	C
416BRN	15945	6-32 x 1	Brown	50	250	2000	0.20#	C
416WHT	15950	6-32 x 1	White	50	250	2000	0.20#	C
416ALD	15955	6-32 x 1	Almond	50	250	2000	0.20#	C



Wall Plate Screw Kits... Page B17

APS1 12 Compartment consisting of 450 assorted screws: White, Ivory, Almond, Stainless, Brass & Nylon

APS2 6 Compartment consisting of 450 assorted screws: White, Almond & Ivory



Ground Screws PC 5620

Now With
Multi-Drive



- Steel
- Green Zinc Plated
- 1/4" or 5/16" Head
- Leader or Thread Cutting Point
- Hex/Slotted/Phillips/Square

Ground screws are plated green for identification purposes and are used for grounding pigtails or wire. They have either a 1/4" or 5/16" head with Hex/Slotted/Phillips/Square drive. The 1/4" (1032G & 1032GTP) has a leader point; the 5/16" (1032TC & 1032TCTP) has a thread cutting point.

CAT NO	UPC	DESCRIPTION	HEX SIZE	SCREW SIZE	STD	MSTR	WT/STD	UNIT
1032G	14107	Leader Point Hex/Slotted/Phillips/Square	1/4"	10-32 x 3/8"	100	1000	0.44#	C
1032GTP	14108	Tuff Pack 	1/4"	10-32 x 3/8"	500	3000	4.20#	C
1032TC	14109	Thread Cutting Pt. Hex/Slotted/Phillips/Square	5/16"	10-32 x 3/8"	100	1000	0.50#	C
1032TCTP	14111	Tuff Pack 	5/16"	10-32 x 3/8"	500	3000	4.86#	C

See new products at Ihdottie.com

Dottie

