



Pan Head Slotted/Phillips (2 Way) Sheet Metal Screws - Zinc Plated - PC 4000

Pan head combo (slotted/phillips) sheet metal screws will tap their own mating threads when driven into preformed holes in metal. Length is determined from the base of the fastener head.

- Sheet Metal Screws
- Zinc Plated Steel
- Slotted/Phillips
- Invincibox™ Up To 2"

CAT NO	UPC	SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
2WS612	58162	6 x 1/2	100	500	4000	0.20#	C
2WS634	58164	6 x 3/4	100	500	4000	0.27#	C
2WS61	58166	#6 6 x 1	100	500	4000	0.34#	C
2WS6114	58168	6 x 1-1/4	100	500	4000	0.42#	C
2WS6112	58170	6 x 1-1/2	100	500	4000	0.49#	C
2WS62	58172	6 x 2	100	500	3000	0.64#	C
2WS812	58150	8 x 1/2	100	500	4000	0.31#	C
2WS834	58152	8 x 3/4	100	500	4000	0.41#	C
2WS81	58154	#8 8 x 1	100	500	4000	0.51#	C
2WS8114	58156	8 x 1-1/4	100	500	4000	0.61#	C
2WS8112	58158	8 x 1-1/2	100	500	3000	0.69#	C
2WS82	58160	8 x 2	100	500	3000	0.89#	C
2WS1012	58200	10 x 1/2	100	500	4000	0.43#	C
2WS1034	58202	10 x 3/4	100	500	4000	0.54#	C
2WS101	58204	#10 10 x 1	100	500	4000	0.69#	C
2WS10114	58206	10 x 1-1/4	100	500	3000	0.80#	C
2WS10112	58208	10 x 1-1/2	100	500	3000	0.91#	C
2WS102	58210	10 x 2	50	250	1500	0.63#	C
2WS1212	58174	12 x 1/2	100	500	4000	0.61#	C
2WS1234	58176	12 x 3/4	100	500	3000	0.81#	C
2WS121	58178	#12 12 x 1	100	500	3000	0.96#	C
2WS12114	58180	12 x 1-1/4	100	500	3000	1.15#	C
2WS12112	58182	12 x 1-1/2	100	500	3000	1.30#	C
2WS122	58184	12 x 2	50	250	1500	0.81#	C
2WS1412	58186	14 x 1/2	100	500	3000	0.86#	C
2WS1434	58188	14 x 3/4	100	500	3000	1.09#	C
2WS141	58190	#14 14 x 1	100	500	3000	1.28#	C
2WS14114	58192	14 x 1-1/4	100	500	3000	1.57#	C
2WS14112	58194	14 x 1-1/2	50	250	1500	0.89#	C
2WS142	58196	14 x 2	50	250	1500	1.11#	C
2WST834	58161	#8 Tuff Pack 8 x 3/4	500		3000	2.24#	C
2WST81	58163	8 x 1	500		3000	3.29#	C
2WST1034	58165	10 x 3/4	500		3000	3.70#	C
2WST101	58167	#10 Tuff Pack 10 x 1	500		3000	3.60#	C



Pan Head Phillips Sheet Metal Screws Stainless Steel - PC 4010

Stainless steel pan head phillips sheet metal screws will tap their own mating threads when driven into preformed holes in metal. Length is determined from the base of the fastener head. Stainless steel resists corrosion and is ideal for applications where chemical resistance is required.

- Sheet Metal Screws
- Phillips
- 18-8 Stainless Steel
- Invincibox™ Up To 2"

CAT NO	UPC	SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
PHSMSS612	70204	6 x 1/2	100	500	4000	0.20#	C
PHSMSS634	70206	6 x 3/4	100	500	4000	0.27#	C
PHSMSS61	70208	#6 6 x 1	100	500	4000	0.34#	C
PHSMSS6114	70210	6 x 1-1/4	100	500	4000	0.42#	C
PHSMSS6112	70212	6 x 1-1/2	100	500	4000	0.49#	C
PHSMSS62	70214	6 x 2	100	500	3000	0.64#	C
PHSMSS812	70220	8 x 1/2	100	500	4000	0.31#	C
PHSMSS834	70222	8 x 3/4	100	500	4000	0.41#	C
PHSMSS81	70224	#8 8 x 1	100	500	4000	0.51#	C
PHSMSS8114	70226	8 x 1-1/4	100	500	4000	0.61#	C
PHSMSS8112	70228	8 x 1-1/2	100	500	3000	0.69#	C
PHSMSS82	70230	8 x 2	100	500	3000	0.89#	C
PHSMSS1012	70240	10 x 1/2	100	500	4000	0.43#	C
PHSMSS1034	70242	10 x 3/4	100	500	4000	0.54#	C
PHSMSS101	70244	#10 10 x 1	100	500	4000	0.69#	C
PHSMSS10114	70246	10 x 1-1/4	100	500	3000	0.80#	C
PHSMSS10112	70248	10 x 1-1/2	100	500	3000	0.91#	C
PHSMSS102	70250	10 x 2	50	250	1500	0.85#	C