



## Flat Head Square/Phillips Machine Screws Zinc Plated - PC 4020

Flat head machine screws provide a flush surface.  
Length is determined from the top of the fastener head.

- Machine Screws
- Flat Head
- Square/Phillips
- Zinc Plated Steel
- Invincibox™ Up To 2"

CAT NO	UPC	SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
FMDD63212	65482	6-32 x 1/2	100	500	4000	0.20#	C
FMDD63234	65486	6-32 x 3/4	100	500	4000	0.26#	C
FMDD6321	65490	<b>6-32</b> 6-32 x 1	100	500	4000	0.33#	C
FMDD632114	65494	6-32 x 1-1/4	100	500	4000	0.40#	C
FMDD632112	65498	6-32 x 1-1/2	100	500	4000	0.49#	C
FMDD6322	65503	6-32 x 2	100	500	3000	0.62#	C
FMDD83212	65509	8-32 x 1/2	100	500	4000	0.29#	C
FMDD83234	65513	8-32 x 3/4	100	500	4000	0.40#	C
FMDD8321	65517	<b>8-32</b> 8-32 x 1	100	500	4000	0.50#	C
FMDD832114	65521	8-32 x 1-1/4	100	500	4000	0.61#	C
FMDD832112	65525	8-32 x 1-1/2	100	500	3000	0.72#	C
FMDD102412	65435	10-24 x 1/2	100	500	4000	0.49#	C
FMDD102434	65436	10-24 x 3/4	100	500	4000	0.62#	C
FMDD10241	65440	<b>10-24</b> 10-24 x 1	100	500	4000	0.75#	C
FMDD1024114	65444	10-24 x 1-1/4	100	500	4000	0.95#	C
FMDD1024112	65448	10-24 x 1-1/2	100	500	3000	1.03#	C
FMDD10242	65452	10-24 x 2	50	250	1500	0.66#	C
FMDD103212	65460	<b>10-32</b> 10-32 x 1/2	100	500	4000	0.49#	C
FMDD10321	65466	10-32 x 1	100	500	4000	0.75#	C
FMDD1412	65476	1/4 x 1/2	100	500	4000	0.76#	C
FMDD1434	65402	1/4 x 3/4	100	500	3000	1.19#	C
FMDD141	65406	<b>1/4-20</b> 1/4 x 1	100	500	3000	1.45#	C
FMDD14114	65410	1/4 x 1-1/4	100	500	3000	1.69#	C
FMDD14112	65414	1/4 x 1-1/2	50	250	1500	0.99#	C
FMDD142	65418	1/4 x 2	50	250	1500	1.21#	C
FMDD14212	65422	1/4 x 2-1/2	100		1000	2.73#	C



## Truss Head Slotted Stove Bolts with Nuts Zinc Plated - PC 4022

Stove bolts have a truss head and are furnished with hex nuts. The head projects above the material surface. This head style is used when clearance is an important factor. Length is determined from the base of the fastener head.

- Stove Bolts
- Truss Head
- Slotted
- Includes Nuts
- Zinc Plated Steel

CAT NO	UPC	SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
SB31612	57900	3/16 x 1/2	100	500	4000	0.89#	C
SB31634	57902	3/16 x 3/4	100	500	4000	1.04#	C
SB3161	57904	<b>3/16 (10-24)</b> 3/16 x 1	100	500	3000	1.18#	C
SB316114	57906	3/16 x 1-1/4	100	500	3000	1.33#	C
SB316112	57908	3/16 x 1-1/2	100	500	3000	1.47#	C
SB3162	57910	3/16 x 2	100	500	3000	1.76#	C
SB1412	57950	1/4 x 1/2	100	500	3000	1.74#	C
SB1434	57952	1/4 x 3/4	100	500	3000	2.11#	C
SB141	57954	<b>1/4-20</b> 1/4 x 1	100	500	3000	2.26#	C
SB14114	57956	1/4 x 1-1/4	100	500	1000	2.52#	C
SB14112	57958	1/4 x 1-1/2	100		1000	2.78#	C
SB142	57960	1/4 x 2	100		1000	3.30#	C

