

# Nylon KO Bushings PC 6100



- 105° C
- Snap In
- Reusable

Nylon KO bushings are snapped into punched holes in panels to protect wires from the rough edges.

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
1210D	12100	1/2"	100	1000	0.45#	C
1211D	12110	3/4"	100	1000	0.66#	C
1212D	12120	1"	100	1000	0.99#	C
1213D	12130	1-1/4"	50	500	0.70#	C
1214D	12140	1-1/2"	25	250	0.46#	C
1215D	12150	2"	25	250	0.93#	C
1216D	12160	2-1/2"	25	250	1.20#	C

# Anti-Short Bushings PC 5680



- Plastic
- Fits Armored Cable
- Prevents Shorts

Anti-Short bushings are used to protect wire insulation from the jagged or sharp cut edges of BX or flex. Priced per 100 pieces.

CAT NO	UPC	FLEX	CABLE SIZE	PKG	STD	MSTR	WT/STD	UNIT
0	11600	5/16"	14/2, 14/3, 12/2	100	1000	1000	0.75#	C
1	11601	3/8"	14/4, 6/1,4/1, 12/3	100	1000	1000	0.30#	C
2	11602	7/16"	12/4, 10/2, 10/3, 2/1	50	500	500	0.35#	C
3	11603	1/2"	10/4, 8/2, 8/3, 1/1	50	500	500	0.40#	C
4	11604	3/4"	8/4, 6/2, 6/3, 4/2, 4/3	50	500	500	0.40#	C

# K.O. Seals PC 5440



- Snap In
- Steel
- Zinc Plated

Snap in K.O. seals are used to seal up holes punched in panels or knockouts from outlet boxes. They are held in place by spring tension. Available in sizes from 1/2" thru 2".

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
KO50	16000	1/2"	100	1000	1.44#	C
KO75	16010	3/4"	100	1000	1.62#	C
KO100	16020	1"	100	500	2.10#	C
KO125	16030	1-1/4"	50	100	1.45#	C
KO150	16040	1-1/2"	50	50	2.14#	C
KO200	16050	2"	25	25	1.44#	C

# Three Piece K.O. Seals PC 5450



- Assembled\*
- Includes Screw and Threaded Strap
- Steel
- Zinc Plated

Three piece K.O. seals are used to seal up holes punched in panels or knockouts from outlet boxes. They are held in place by a screw inserted through the seal into a threaded strap on the opposite side of the opening. Available in sizes from 1/2" thru 6". Three piece K.O. seals are embossed to centralize in knockout. Installs from the inside or outside of any box without rearranging wires. One screw secures unit. Size is stamped into seal.

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
D10S*	10240	1/2"	100	100	2.62#	C
D20S*	10242	3/4"	50	50	1.73#	C
D30S*	10244	1"	25	25	1.33#	C
D40S	10246	1-1/4"	25	25	1.74#	C
D50S	10248	1-1/2"	10	10	1.03#	C
D60S	10250	2"	10	10	1.46#	C
D70S	10252	2-1/2"	10	10	2.16#	C
D80S	10254	3"	10	10	3.11#	C
D90S	10256	3-1/2"	10	10	3.97#	C
D100S	10258	4"	10	10	5.81#	C
D110S	10260	4-1/2"	10	10	10.45#	C
D120S	10262	5"	10	10	13.33#	C
D130S	10264	6"	10	10	14.10#	C