

Flat Head Slotted Machine Screws

Zinc Plated - PC 4000



- Machine Screws
- Flat Head
- Slotted
- Zinc Plated Steel
- Invincibox™ Up To 2"

Flat head machine screws provide a flush surface. Length is determined from the top of the fastener head.

CAT NO	UPC	SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
FM63238	65000	6-32 x 3/8	100	500	4000	0.19#	C
FM63212	65002	6-32 x 1/2	100	500	4000	0.24#	C
FM63234	65004	6-32 x 3/4	100	500	4000	0.30#	C
FM6321	65006	6-32 x 1	100	500	4000	0.38#	C
FM632114	65008	6-32 6-32 x 1-1/4	100	500	4000	0.44#	C
FM632112	65010	6-32 x 1-1/2	100	500	4000	0.52#	C
FM6322	65012	6-32 x 2	100	500	3000	0.65#	C
FM632212	65014	6-32 x 2-1/2	100	500	1000	0.79#	C
FM6323	65016	6-32 x 3	100		1000	0.97#	C
FM83238	65050	8-32 x 3/8	100	500	4000	0.29#	C
FM83212	65052	8-32 x 1/2	100	500	4000	0.34#	C
FM83234	65054	8-32 x 3/4	100	500	4000	0.42#	C
FM8321	65056	8-32 x 1	100	500	4000	0.52#	C
FM832114	65058	8-32 8-32 x 1-1/4	100	500	4000	0.64#	C
FM832112	65060	8-32 x 1-1/2	100	500	3000	0.77#	C
FM8322	65062	8-32 x 2	100	500	3000	0.94#	C
FM832212	65064	8-32 x 2-1/2	100		1000	1.25#	C
FM8323	65066	8-32 x 3	100		1000	1.36#	C
FM102438	65100	10-24 x 3/8	100	500	4000	0.36#	C
FM102412	65102	10-24 x 1/2	100	500	4000	0.45#	C
FM102434	65104	10-24 x 3/4	100	500	4000	0.57#	C
FM10241	65106	10-24 x 1	100	500	4000	0.73#	C
FM1024114	65108	10-24 10-24 x 1-1/4	100	500	4000	0.86#	C
FM1024112	65110	10-24 x 1-1/2	100	500	3000	0.94#	C
FM10242	65112	10-24 x 2	50	250	1500	0.65#	C
FM10243	65116	10-24 x 3	100		1000	2.03#	C
FM103238	65150	10-32 x 3/8	100	500	4000	0.37#	C
FM103212	65152	10-32 x 1/2	100	500	4000	0.42#	C
FM103234	65154	10-32 x 3/4	100	500	4000	0.57#	C
FM10321	65156	10-32 x 1	100	500	4000	0.75#	C
FM1032114	65158	10-32 10-32 x 1-1/4	100	500	3000	0.87#	C
FM1032112	65160	10-32 x 1-1/2	100	500	3000	0.99#	C
FM10322	65162	10-32 x 2	50	250	1500	0.68#	C
FM10323	65151	10-32 x 3	100		1000	2.03#	C
FM1438	65200	1/4 x 3/8	100	500	4000	0.69#	C
FM1412	65202	1/4 x 1/2	100	500	4000	0.78#	C
FM1434	65204	1/4 x 3/4	100	500	3000	1.12#	C
FM141	65206	1/4 x 1	100	500	3000	1.48#	C
FM14114	65208	1/4-20 1/4 x 1-1/4	100	500	3000	1.51#	C
FM14112	65210	1/4 x 1-1/2	50	250	1500	0.93#	C
FM142	65212	1/4 x 2	50	250	1500	1.13#	C
FM14212	65214	1/4 x 2-1/2	100		1000	2.73#	C
FM143	65216	1/4 x 3	100		1000	3.44#	C
FM144	65218	1/4 x 4	100		1000	3.99#	C
FM3834	65250	3/8 x 3/4	100		1000	3.00#	C
FM381	65252	3/8 x 1	100		1000	3.37#	C
FM38114	65254	3/8-16 3/8 x 1-1/4	100		1000	4.82#	C
FM38112	65256	3/8 x 1-1/2	100		1000	5.22#	C
FM382	65258	3/8 x 2	100		1000	6.16#	C
FM38212	65260	3/8 x 2-1/2	100		400	6.89#	C
FM383	65262	3/8 x 3	100		400	8.52#	C
FM384	65264	3/8 x 4	100		400	10.94#	C
FMT6321	65020	6-32 Tuff Pack 6-32 x 1	500		3000	2.05#	C
FMT632114	65021	6-32 x 1-1/4	500		3000	2.35#	C
FMT632112	65022	6-32 x 1-1/2	500		3000	2.75#	C
FMT6322	65023	6-32 x 2	300		3000	3.40#	C

