



## Wall Dog - Phillips / Square / Hex PC 4731



- Self-drills small hole in wallboard
- Installs quickly and easily with a Phillips screwdriver
- Can be easily backed-out
- No need for shields
- Case hardened steel anchor
- No hole spotting
- Installs in wallboard, plywood, concrete, hollow or grout filled block, brick and plaster
- No second step, installs directly through fixture into wallboard
- Patented design provides for smooth entry, clean cutting and a powerful hold
- Thread design prevents spinning and stripping
- Heat treated point penetrates metal and wood studs
- When removed it leaves a much smaller hole than toggles or other systems

CAT NO	UPC		DESCRIPTION	STD	MSTR	WT/STD	UNIT
WDOG	31395		100 Chrome Phillips Wall Dog 1 3/16" Carbide Tip Drill Bit 1 IB2PL Phillips Power Bit	1	10	1.67#	Ea
WDOGW	31396		100 White Phillips Wall Dog 1 3/16" Carbide Tip Drill Bit 1 IB2PL Phillips Power Bit	1	10	1.67#	Ea
SQDOG	16290		100 Chrome Square Wall Dog 1 3/16" Carbide Tip Drill Bit 1 IB2L Square Drive Power Bit	1	10	1.67#	Ea
HXDOG	81016		100 Chrome Hex Drive Wall Dog 1 3/16" Carbide Tip Drill Bit 1 MT10 Magnetic Hex Bit	1	10	1.67#	Ea



## Wall Driller Kits • Phillips / Square / Wafer PC 4730

- Easy To Spot
- Reusable
- Deep Threads
- Includes Bit
- 50 Phillips/Square/Wafer Sheet Metal Screws
- 50 Zinc or Nylon Anchors
- Display or Tuff Pack

CAT NO	UPC	D-DISPLAY PACK T-TUFF PACK		SCREW SIZE	ANCHOR	BIT	STD	MSTR	WT/STD	UNIT
<b>Phillips / Slotted</b>										
WDK6	29780	D		6 x 1"	Zinc	IB1P	1	10	0.75#	Ea
WDK6T	29855	T		6 x 1"	Zinc	IB1P	1	10	0.75#	Ea
WDK6N	29781	D		6 x 1"	Nylon	IB1P	1	10	0.46#	Ea
WDK6NT	29857	T		6 x 1"	Nylon	IB1P	1	10	0.46#	Ea
WDK8	29786	D		8 x 1-1/4"	Zinc	IB2P	1	10	1.33#	Ea
WDK8T	29862	T		8 x 1-1/4"	Zinc	IB2P	1	10	1.33#	Ea
WDK8N	29787	D		8 x 1-1/4"	Nylon	IB2P	1	10	0.70#	Ea
WDK8NT	29864	T		8 x 1-1/4"	Nylon	IB2P	1	10	0.46#	Ea
<b>Square Drive</b>										
WDK6SQ	29790	D		6 x 1"	Zinc	IB1	1	10	0.75#	Ea
WDK6SQT	29866	T		6 x 1"	Zinc	IB1	1	10	0.75#	Ea
WDK6NSQ	29791	D		6 x 1"	Nylon	IB1	1	10	0.46#	Ea
WDK6NSQT	29868	T		6 x 1"	Nylon	IB1	1	10	0.46#	Ea
WDK8SQ	29796	D		8 x 1-1/4"	Zinc	IB2	1	10	1.33#	Ea
WDK8SQT	29872	T		8 x 1-1/4"	Zinc	IB2	1	10	1.33#	Ea
WDK8NSQ	29797	D		8 x 1-1/4"	Nylon	IB2	1	10	0.70#	Ea
WDK8NSQT	29874	T		8 x 1-1/4"	Nylon	IB2	1	10	0.46#	Ea
<b>Wafer Head Phillips / Square Drive</b>										
WDK8W	81518	D		8 x 1-1/4"	Zinc	IB2P	1	10	1.33#	Ea
WDK8WT	81519	T		8 x 1-1/4"	Zinc	IB2P	1	10	1.33#	Ea
WDK8NW	81520	D		8 x 1-1/4"	Nylon	IB2P	1	10	0.70#	Ea
WDK8NWT	81521	T		8 x 1-1/4"	Nylon	IB2P	1	10	0.70#	Ea
WDK8WSQ	81522	D		8 x 1-1/4"	Zinc	IB2	1	10	1.33#	Ea
WDK8WSQT	81523	T		8 x 1-1/4"	Zinc	IB2	1	10	1.33#	Ea
WDK8NWSQ	81524	D		8 x 1-1/4"	Nylon	IB2	1	10	0.70#	Ea
WDK8NWSQT	81525	T		8 x 1-1/4"	Nylon	IB2	1	10	0.46#	Ea

