

Hacksaw Frame PC 6470



- Use as Jab or Compass Saw
- 45° & 90° Miter Angle
- High Leverage Tension Arm
- Blade Storage in Handle
- Industrial Quality Die Cast
- Made In USA

This versatile hacksaw has a heavy duty cast aluminum handle and steel crossbar. Lightweight and well balanced for greater control.

CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
F4	28975	Industrial Quality Hacksaw Frame	1	6	1.470#	Ea

Hacksaw Blades PC 6580

- Bi Metal
- Boxed or Pouch
- Industrial Quality
- Caution! Always Wear Eye Protection

Bi-metal hacksaw blades cut tough and hard material fast and outlasts standard carbon blades by a factor of three to one. Bi-metal blades offer a super sharp high speed steel cutting edge, laser welded to a flexible alloy back. Bi-metal blades offer straight cuts and long life in high tension frames and allow the greatest possible user safety.

CAT NO	UPC	LENGTH	TPI	STD	MSTR	WT/STD	UNIT
HSB18T*	29350	12"	18	10	100	0.430#	Ea
HSB18TB	29340	12"	18	100	100	4.300#	Ea
HSB24T*	29355	12"	24	10	100	0.430#	Ea
HSB24TB	29343	12"	24	100	100	4.300#	Ea
HSB32T*	29360	12"	32	10	100	0.430#	Ea
HSB32TB	29345	12"	32	100	100	4.300#	Ea

* Pouch

PVC Saw & Replacement Blades PC 6560



- Tooth Design Cuts On Both Strokes
- Filed Teeth
- 12" Handle With Blade
- 18" Handle With Blade
- Caution! Always Wear Eye Protection

The PVC Bi-Saw is designed for PVC and cuts on both the front and back stroke. The offset handle allows cutting at ground level while permitting hand clearance. The die cast, offset handle is interchangeable with most popular brands of replacement blades.

CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
PVC12BH	29380	12" Handle & Blade	1	5	0.660#	Ea
PVC18BH	29382	18" Handle & Blade	1	5	0.770#	Ea
12BLD	29384	12" Replacement Blade Only	1	5	0.330#	Ea
18BLD	29386	18" Replacement Blade Only	1	5	0.460#	Ea

Snaggletooth Pro Saw PC 6559



- Easily Cuts Wallboard, Drywall, Plywood, & Plastic
- Blade Cuts In Both Directions
- Laser Cut Triple Ground Teeth
- Triangular Handle

The Snaggletooth Pro Saw is the right tool for cutting openings for electrical outlets, and the hardened tip penetrates drywall easily eliminating the need to drill.

CAT NO	UPC	DESCRIPTION	LENGTH	STD	MSTR	WT/STD	UNIT
SNG6	42092	Snaggletooth Pro Saw	6" Blade/ 12" Overall	1	12	0.350#	Ea