



Kodiak



Razor



Komodo



Protective Eyewear PC 6610

- Exceeds ANSI Z87.1 & CSA Z94.3 Safety Standards
- 100% UV & UVB Protection Against Harmful Radiation
- Ultra Light, Durable & Precise Fit Frames
- Impact Resistant Polycarbonate Lens
- Distortion Free 2.2 mm Lens For Optimum Clarity
- Exceptional Peripheral Vision Protection
- Variety of Coated Lens Tints
- Hangable Display Pack

Industrial safety eyewear is designed to protect you. Available in a variety of styles, finishes and lens color tints, they are designed down to the smallest detail to provide optimal performance with state of the art comfort, style and protection.

CAT NO	UPC	STYLE	FRAME	LENS	STD	MSTR	WT/STD	UNIT
EKOD110	10923	Kodiak	Matte Black	Gray	1	10	0.11#	Ea
EKOD175	10924	Kodiak	Matte Black	Dark Blue Mirror	1	10	0.11#	Ea
EKOD440	10925	Kodiak	Crystal Blue	Gray Mirror	1	10	0.11#	Ea
EKOD685	10926	Kodiak	Shiny Silver	Dark Blue Mirror	1	10	0.11#	Ea
EKOD740	10927	Kodiak	Crystal Red	Gray Mirror	1	10	0.11#	Ea
ERAZ100	11984	Razor	Matte Black	Clear	1	10	0.11#	Ea
ERAZ110	11985	Razor	Matte Black	Gray	1	10	0.11#	Ea
ERAZ120	11986	Razor	Matte Black	Yellow	1	10	0.11#	Ea
ERAZ160	11987	Razor	Matte Black	Dark Brown Mirror	1	10	0.11#	Ea
ERAZ175	11988	Razor	Matte Black	Dark Blue Mirror	1	10	0.11#	Ea
EKMD000	81814	Komodo	Crystal Clear	Clear	1	10	0.11#	Ea
EKMD110	81815	Komodo	Crystal Black	Gray	1	10	0.11#	Ea
EKMD550	81816	Komodo	Amber	Brown	1	10	0.11#	Ea
EKMD840	81817	Komodo	Gun Metal Gray	Gray Mirror	1	10	0.11#	Ea
EKMD870	81818	Komodo	Gun Metal Lt. Blue	Blue Mirror	1	10	0.11#	Ea



Softframe Goggles PC 6610

Soft, clear vinyl Goggle with universal bridge provides all day comfort and exceptional protection against dust and flying debris. Around-the-lens ventilation minimizes lens fogging. Comfortable over prescription glasses or when worn alone.

- Clear Anti-Fog Lens
- Cap Vented Clear Softframe

CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
206F	40150	Softframe Goggle	1	10	0.26#	Ea



Ear Protection PC 6615

One pair per polybag. Packed 200 pair per dispenser box.

- ANSI S3.19-1974
- Noise Reduction Rate NRR 30db
- Low Pressure Foam Plugs
- Self Adjusting
- Non Allergenic
- Non Irritating

CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
MLE200	11645	MaxLite Ear Plugs	200 Pr	200 Pr	0.94#	Ea Pair

Shoe Covers PC 6771



- Anti-Static
- Impervious Material
- Non-linting
- EZ On-EZ Off

CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
SC	59880	50 Shoe Covers in Jar	1	10	0.90#	Ea

