





Now With Multi-Drive

Ground Screws PC 5620

Ground screws are plated green for identification purposes and are used for grounding pigtails or wire. They have either a 1/4" or 5/16" head with Hex/Slotted/Phillips/Square drive. The 1/4" (1032G & 1032GTP) has a leader point; the 5/16" (1032TC & 1032TCTP) has a thread cutting point.

- Steel
- Green Zinc Plated
- 1/4" or 5/16" Head
- Leader or Thread Cutting Point
- Hex/Slotted/Phillips/Square

| CAT NO | UPC | DESCRIPTION | HEX SIZE | SCREW SIZE | STD | MSTR | WT/STD | UNIT |
|----------|-------|--|----------|--------------|-----|------|--------|------|
| 1032G | 14107 | Leader Point Hex/Slotted/Phillips/Square | 1/4" | 10-32 x 3/8" | 100 | 1000 | 0.44# | C |
| 1032GTP | 14108 | Tuff Pack  | 1/4" | 10-32 x 3/8" | 500 | 3000 | 4.20# | C |
| 1032TC | 14109 | Thread Cutting Pt. Hex/Slotted/Phillips/Square | 5/16" | 10-32 x 3/8" | 100 | 1000 | 0.50# | C |
| 1032TCTP | 14111 | Tuff Pack  | 5/16" | 10-32 x 3/8" | 500 | 3000 | 4.86# | C |



Now With Multi-Drive

Ground Pigtails PC 5630

Ground pigtails are used for grounding receptacles to steel boxes.

- Green Zinc Plated Ground Screw
- UL Listed Wire
- Green #12 Ga. Solid Copper Wire
- 7-1/2", 10-1/2" or 12-1/2" Lengths
- 1/4" Hex/Slotted/Phillips/Square with (Leader Point)


| CAT NO | UPC | SIZE | GAUGE | STD | MSTR | WT/STD | UNIT |
|--------|-------|---------|-------|-----|------|--------|------|
| GP650 | 16100 | 7-1/2" | 12 Ga | 250 | 2000 | 4.90# | C |
| GP1050 | 16102 | 10-1/2" | 12 Ga | 250 | 2000 | 6.56# | C |
| GP1250 | 16103 | 12-1/2" | 12 Ga | 250 | 1000 | 7.44# | C |



Ground Clips PC 5640

Ground Clips are intended to be pressed on the top edge of a box to hold a No.10, 12, or 14AWG copper or No.10, or 12AWG aluminum grounding conductor against the side wall. This clip may be used for connecting the grounding conductor of nonmetallic sheathed cable to outlet boxes or for connecting the grounding jumper from a receptacle to an outlet.

- UL Listed
- Zinc Plated
- Holds 10, 12, or 14 Ga. Copper Wire
- Holds 10, or 12 Ga. Aluminum Wire

| CAT NO | UPC | STD | MSTR | WT/STD | UNIT |
|--------|-------|--|------|--------|-------|
| GC | 27050 | 100 | 1000 | 0.38# | C |
| GCTP | 27051 | Tuff Pack  | 500 | 3000 | 1.90# |



Copper Crimp Sleeves PC 5650

Copper Crimp Sleeves are used to group and terminate copper wires and provide a vibration resistant connection. Copper requires crimping pressure and resists corrosion.

- UL Listed
- Solid Copper
- 18 to 10 Ga. Wire
- 18 to 8 Ga. Wire

| CAT NO | UPC | WIRE GAUGE | STD | MSTR | WT/STD | UNIT |
|---------|-------|--|-----|------|--------|------|
| CS410 | 27755 | 18-10 AWG | 100 | 1000 | 0.24# | C |
| CS410TP | 27756 | Tuff Pack  | 500 | 3000 | 1.15# | C |
| CS411 | 27760 | 18-8 AWG | 50 | 500 | 0.24# | C |