



Die Cast Liquid Tite Connectors PC 5460

Die cast liquid tite connectors are used to connect metallic & non-metallic liquid tite conduit into an enclosure.

- UL Listed
- Zinc Die Cast
- Straight & 90°
- Insulated & Non Insulated

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
LT38	11000	3/8"	25	250	3.22#	C
LT50	11005	1/2"	25	250	3.65#	C
LT75	11010	3/4"	10	100	2.19#	C
LT100	11015	Straight 1"	5	50	1.74#	C
LT125	11020	1-1/4"	5	50	2.69#	C
LT150	11025	1-1/2"	2	20	1.26#	C
LT200	11030	2"	2	20	1.60#	C
<hr/>						
LT9038	11200	3/8"	10	100	2.17#	C
LT9050	11205	1/2"	10	100	2.97#	C
LT9075	11210	3/4"	10	100	2.73#	C
LT90100	11215	90° 1"	5	50	2.26#	C
LT90125	11220	1-1/4"	5	50	3.92#	C
LT90150	11225	1-1/2"	2	20	2.12#	C
LT90200	11230	2"	2	20	2.62#	C
<hr/>						
LT38I	11100	3/8"	25	250	3.86#	C
LT50I	11105	1/2"	25	250	3.32#	C
LT75I	11110	3/4"	10	100	2.37#	C
LT100I	11115	1"	5	50	1.84#	C
LT125I	11120	Straight 1-1/4"	5	50	2.66#	C
LT150I	11125	Insulated 1-1/2"	2	20	1.24#	C
LT200I	11130	2"	2	20	1.64#	C
LT250I	11135	2-1/2"	1	1	1.74#	C
LT300I	11140	3"	1	1	2.68#	C
LT350I	11145	3-1/2"	1	1	3.45#	C
LT400I	11150	4"	1	1	3.87#	C
<hr/>						
LT9038I	11300	3/8"	10	100	2.28#	C
LT9050I	11305	1/2"	10	100	1.98#	C
LT9075I	11310	3/4"	10	100	2.77#	C
LT90100I	11315	1"	5	50	2.26#	C
LT90125I	11320	90° 1-1/4"	5	50	4.09#	C
LT90150I	11325	Insulated 1-1/2"	2	20	2.06#	C
LT90200I	11330	2"	2	20	2.81#	C
LT90250I	11235	2-1/2"	1	1	3.43#	C
LT90300I	11240	3"	1	1	4.72#	C
LT90350I	11245	3-1/2"	1	1	7.33#	C
LT90400I	11250	4"	1	1	8.03#	C



PVC Liquid Tite Connectors PC 5490

PVC liquid tite connectors are used to connect non metallic liquid tite conduit & flexible non-metallic tubing to enclosures. UV rated plastic.

- UL Listed
- PVC With Polypropylene Sealing Ring
- Straight & 90°

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
NLT38	36000	3/8"	25	100	1.92#	C
NLT50	36002	1/2"	25	100	1.34#	C
NLT75	36004	3/4"	25	100	2.38#	C
NLT100	36006	Straight 1"	25	100	2.68#	C
NLT125	36007	1-1/4"	5	25	1.40#	C
NLT150	36009	1-1/2"	5	25	1.42#	C
NLT200	36011	2"	5	25	2.13#	C
<hr/>						
NLT9038	36008	3/8"	10	50	0.89#	C
NLT9050	36010	1/2"	10	50	0.76#	C
NLT9075	36012	3/4"	10	50	1.07#	C
NLT90100	36014	90° 1"	5	25	1.00#	C
NLT90125	36013	1-1/4"	5	25	1.72#	C
NLT90150	36015	1-1/2"	5	25	2.43#	C
NLT90200	36016	2"	5	25	3.41#	C

