

# Bits & Tools PC 6650



Insert and power bits are available in a variety of configurations. Bits of 1" length are insert bits; bits 2" and longer are power bits. Note: MBH Tool is used with insert bits only. Not to be used with power bits.

- Maximum Durability
- Precision Fit Prevents Wear

TOOLS & SPECIALTY ITEMS > BITS & TOOLS

CAT NO	UPC	TYPE	SCREW SIZE	POINT SIZE / LENGTH	STD	MSTR	WT/STD	UNIT
<b>Phillips Pt. Size 0 &amp; 1</b>								
IB0P	60205	Insert Bit	#4	#0 x 1"	10	100	0.100#	Ea
IB1P	60222	Insert Bit	#6	#1 x 1"	10	100	0.100#	Ea
IB1PL	60224	Power Bit	#6	#1 x 2"	10	100	0.230#	Ea
IB1PX	60346	Power Bit	#6	#1 x 3"	5	50	0.170#	Ea
IB1P4	60348	Power Bit	#6	#1 x 4"	5	50	0.236#	Ea
IB1P6	60360	Power Bit	#6	#1 x 6"	5	50	0.360#	Ea
<b>Phillips Pt. Size 2</b>								
IB2P	60226	Insert Bit	#8-10	#2 x 1"	10	100	0.100#	Ea
IB2PL	60228	Power Bit	#8-10	#2 x 2"	10	100	0.230#	Ea
IB2PX	60230	Power Bit	#8-10	#2 x 3"	5	50	0.170#	Ea
IB2P4	60362	Power Bit	#8-10	#2 x 4"	5	50	0.236#	Ea
IB2P6	60364	Power Bit	#8-10	#2 x 6"	5	50	0.360#	Ea
<b>Phillips Pt. Size 3</b>								
IB3P	60232	Insert Bit	#12-14	#3 x 1"	10	100	0.100#	Ea
IB3PL	60234	Power Bit	#12-14	#3 x 2"	5	50	0.230#	Ea
IB3PX	60366	Power Bit	#12-14	#3 x 3"	5	50	0.170#	Ea
IB3P4	60368	Power Bit	#12-14	#3 x 4"	5	50	0.236#	Ea
IB3P6	60370	Power Bit	#12-14	#3 x 6"	5	50	0.360#	Ea
<b>Slotted Pt. Size 0 &amp; 1</b>								
IB0S	60202	Insert Bit	#4	#0 x 1"	10	100	0.100#	Ea
IB1S	60210	Insert Bit	#6	#1 x 1"	10	100	0.100#	Ea
IB1SL	60372	Power Bit	#6	#1 x 2"	10	100	0.230#	Ea
IB1SX	60374	Power Bit	#6	#1 x 3"	5	50	0.170#	Ea
IB1S4	60376	Power Bit	#6	#1 x 4"	5	50	0.236#	Ea
IB1S6	60378	Power Bit	#6	#1 x 6"	5	50	0.360#	Ea
<b>Slotted Pt. Size 2</b>								
IB2S	60212	Insert Bit	#8-10	#2 x 1"	10	100	0.100#	Ea
IB2SL	60214	Power Bit	#8-10	#2 x 2"	10	100	0.230#	Ea
IB2SX	60216	Power Bit	#8-10	#2 x 3"	5	100	0.170#	Ea
IB2S4	60380	Power Bit	#8-10	#2 x 4"	5	50	0.236#	Ea
IB2S6	60382	Power Bit	#8-10	#2 x 6"	5	50	0.360#	Ea
<b>Slotted Pt. Size 3</b>								
IB3S	60218	Insert Bit	#12-14	#3 x 1"	10	100	0.100#	Ea
IB3SL	60384	Power Bit	#12-14	#3 x 2"	10	100	0.230#	Ea
IB3SX	60386	Power Bit	#12-14	#3 x 3"	5	50	0.170#	Ea
IB3S4	60388	Power Bit	#12-14	#3 x 4"	5	50	0.236#	Ea
IB3S6	60390	Power Bit	#12-14	#3 x 6"	5	50	0.360#	Ea
<b>Square Pt. 0 &amp; 1</b>								
IB0	60320	Insert Bit	#4	#0 x 1"	10	100	0.100#	Ea
IB1	60200	Insert Bit	#6	#1 x 1"	10	100	0.100#	Ea
IB1L	60322	Power Bit	#6	#1 x 2"	10	100	0.230#	Ea
IB1X	60324	Power Bit	#6	#1 x 3"	5	50	0.170#	Ea
IB14	60326	Power Bit	#6	#1 x 4"	5	50	0.236#	Ea
IB16	60328	Power Bit	#6	#1 x 6"	5	50	0.360#	Ea
<b>Square Pt. Size 2</b>								
IB2	16940	Insert Bit	#8-10	#2 x 1"	10	100	0.100#	Ea
IB2L	60204	Power Bit	#8-10	#2 x 2"	10	100	0.230#	Ea
IB2X	60330	Power Bit	#8-10	#2 x 3"	5	50	0.170#	Ea
IB24	60332	Power Bit	#8-10	#2 x 4"	5	50	0.236#	Ea
IB26	60334	Power Bit	#8-10	#2 x 6"	5	50	0.360#	Ea
<b>Square Pt. Size 3</b>								
IB3	16943	Insert Bit	#12-14	#3 x 1"	10	100	0.100#	Ea
IB3L	60336	Power Bit	#12-14	#3 x 2"	10	100	0.230#	Ea
IB3X	60338	Power Bit	#12-14	#3 x 3"	5	50	0.170#	Ea
IB34	60340	Power Bit	#12-14	#3 x 4"	5	50	0.236#	Ea
IB36	60342	Power Bit	#12-14	#3 x 6"	5	50	0.360#	Ea