



Flat Head Phillips Wood Screws Brass - PC 4290

Brass flat head wood screws provide a flush surface. Length is determined from the top of the fastener head. Brass is non-magnetic and rust resistant.

- Wood Screws
- Flat Head
- Phillips
- Solid Brass
- Invincibox™ Up To 2"

CAT NO	UPC	SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT	
PHFWB634	38104	#6	6 x 3/4	100	500	4000	0.24#	C
PHFWB61	38106		6 x 1	100	500	4000	0.33#	C
PHFWB834	38204	#8	8 x 3/4	100	500	4000	0.34#	C
PHFWB81	38206		8 x 1	100	500	4000	0.46#	C
PHFWB8114	38208		8 x 1-1/4	100	500	4000	0.58#	C
PHFWB8112	38210		8 x 1-1/2	100	500	3000	0.67#	C
PHFWB82	38212		8 x 2	100	500	3000	0.91#	C
PHFWB1034	38302	#10	10 x 3/4	100	500	4000	0.47#	C
PHFWB101	38304		10 x 1	100	500	4000	0.61#	C
PHFWB10114	38306		10 x 1-1/4	100	500	3000	0.78#	C
PHFWB10112	38308		10 x 1-1/2	100	500	3000	0.92#	C
PHFWB102	38310		10 x 2	50	250	1500	0.60#	C
PHFWB10212	38312		10 x 2-1/2	100		1000	1.56#	C
PHFWB121	38354	#12	12 x 1	100	500	3000	0.81#	C
PHFWB12114	38356		12 x 1-1/4	100	500	3000	0.99#	C
PHFWB12112	38358		12 x 1-1/2	100	500	3000	1.18#	C
PHFWB122	38360		12 x 2	50	250	1500	0.80#	C
PHFWB12212	38362		12 x 2-1/2	100		1000	1.94#	C
PHFWB123	38364		12 x 3	100		1000	2.31#	C



Flat Head Phillips Wood Screws Zinc Plated - PC 4024

Zinc plated flat head wood screws provide a flush surface. Length is determined from the top of the fastener head.

- Wood Screws
- Flat Head
- Phillips
- Zinc Plated
- Invincibox™ Up To 2"

CAT NO	UPC	SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT	
PHFW634	56702	#6	6 x 3/4	100	500	4000	0.24#	C
PHFW61	56704		6 x 1	100	500	4000	0.33#	C
PHFW834	56752	#8	8 x 3/4	100	500	4000	0.34#	C
PHFW81	56754		8 x 1	100	500	4000	0.46#	C
PHFW8114	56756		8 x 1-1/4	100	500	4000	0.58#	C
PHFW8112	56757		8 x 1-1/2	100	500	3000	0.67#	C
PHFW82	56758		8 x 2	100	500	3000	0.91#	C
PHFW1034	56850	#10	10 x 3/4	100	500	4000	0.47#	C
PHFW101	56852		10 x 1	100	500	4000	0.61#	C
PHFW10114	56854		10 x 1-1/4	100	500	3000	0.78#	C
PHFW10112	56856		10 x 1-1/2	100	500	3000	0.92#	C
PHFW102	56858		10 x 2	50	250	1500	1.19#	C
PHFW10212	56860		10 x 2-1/2	100		3000	1.56#	C
PHFW121	56902	#12	12 x 1	100	500	3000	0.81#	C
PHFW12114	56904		12 x 1-1/4	100	500	3000	0.99#	C
PHFW12112	56906		12 x 1-1/2	100	500	3000	1.18#	C
PHFW122	56908		12 x 2	50	250	1500	0.80#	C
PHFW12212	56910		12 x 2-1/2	100		1000	1.94#	C
PHFW123	56912		12 x 3	100		1000	2.31#	C