

Ship Augers PC 6290



- Heat Treated For Long Life
- Self Feeding Screw Point
- 7/16" Hex Shank
- Packed In Display Pouch
- 2 Recesses Provided for Extensions
- Caution! Always Wear Eye Protection

Ship augers are versatile, high quality drills with a self feed screw point for fast, effortless boring and quick chip removal. Designed for drilling through clean lumber or wood where small nails may be encountered.

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
609	14609	9/16"	1	6	0.290#	Ea
610	14610	5/8"	1	6	0.340#	Ea
612	14612	3/4"	1	6	0.390#	Ea
613	14613	13/16"	1	6	0.490#	Ea
614	14614	7/8"	1	6	0.490#	Ea
615	14615	15/16"	1	6	0.510#	Ea
616	14616	1"	1	6	0.570#	Ea
618	14618	1-1/8"	1	6	0.690#	Ea
620	14620	1-1/4"	1	6	0.800#	Ea
622	14622	1-3/8"	1	6	0.900#	Ea
624	14624	1-1/2"	1	6	1.010#	Ea
Short						
1809	21809	9/16"	1	6	0.750#	Ea
1810	21810	5/8"	1	6	0.810#	Ea
1812	21812	3/4"	1	6	0.990#	Ea
1813	21813	13/16"	1	6	1.170#	Ea
1814	21814	7/8"	1	6	1.170#	Ea
1815	21815	15/16"	1	6	1.210#	Ea
1816	21816	1"	1	6	1.400#	Ea
1818	21818	1-1/8"	1	6	1.660#	Ea
1820	21820	1-1/4"	1	6	2.050#	Ea
1822	21822	1-3/8"	1	6	2.280#	Ea
1824	21824	1-1/2"	1	6	2.610#	Ea
Long						

Ship Auger & Speed D Feed Extensions PC 6310



- Forged From High Grade Steel
- Accommodates 7/16" Diameter Shanks
- Add 5-1/2" to 24" In Length
- Heavy Duty Double Set Screw Lock

Extensions are used where additional reach is required.

CAT NO	UPC	LENGTH	SHANK DIA	STD	MSTR	WT/STD	UNIT
X5	21955	5-1/2"	7/16"	1	6	0.500#	Ea
X9	22009	9"	7/16"	1	6	0.690#	Ea
X12	21956	12"	7/16"	1	6	0.950#	Ea
X18	22018	18"	7/16"	1	6	1.200#	Ea
X24	22024	24"	7/16"	1	6	1.460#	Ea

Auger Bit File PC 6291



- Professional Grade
- Caution! Always Wear Eye Protection

Specially designed to sharpen auger bits for longer cutting life.

CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
AF7	11630	7" Auger Bit File	1	6	0.040#	Ea