



Spade Drill Bits PC 6270

Spade drills are used for boring hardwoods, softwood, plywood and drywall. Fully heat treated to extend bit life and individually stamped with size.

- Cold Forged
- Machine Finish Cutting Groove
- Rust Protection
- Wing Tip Design
- Precision Ground Hex Shank
- Caution! Always Wear Eye Protection

CAT NO	UPC	SIZE	LENGTH	STD	MSTR	WT/STD	UNIT
Packed in a Hanging Pouch							
SPD14	21700	1/4"	6"	1	6	0.060#	Ea
SPD516	21702	5/16"	6"	1	6	0.100#	Ea
SPD38	21704	3/8"	6"	1	6	0.100#	Ea
SPD716	21706	7/16"	6"	1	6	0.100#	Ea
SPD12	21708	1/2"	6"	1	6	0.100#	Ea
SPD916	21710	9/16"	6"	1	6	0.100#	Ea
SPD58	21712	5/8"	6"	1	6	0.100#	Ea
SPD1116	21714	11/16"	6"	1	6	0.110#	Ea
SPD34	21716	3/4"	6"	1	6	0.110#	Ea
SPD1316	21718	13/16"	6"	1	6	0.100#	Ea
SPD78	21720	7/8"	6"	1	6	0.110#	Ea
SPD1516	21722	15/16"	6"	1	6	0.120#	Ea
SPD1	21724	1"	6"	1	6	0.110#	Ea
SPD118	21726	1-1/8"	6"	1	6	0.130#	Ea
SPD114	21728	1-1/4"	6"	1	6	0.130#	Ea
SPD138	21730	1-3/8"	6"	1	6	0.140#	Ea
SPD112	21732	1-1/2"	6"	1	6	0.150#	Ea



Bell Hanger Drills PC 6280

Bell hanger drills are used to drill and fish small gauge wires. After drilling through the stud or header, a wire is attached to the fish hole in the flute and the drill is retracted, pulling the wire through. Bell hangers are available in a variety of diameters and lengths and are suitable for telephone installations, security and cable applications.

- Fish Hole In Flute For Pulling Wire
- Tapered For Quick Chip Clearance
- One Per Display Pouch
- Aggressive Point For Fast Drilling In Wood & Metal
- Caution! Always Wear Eye Protection

CAT NO	UPC	SIZE	LENGTH	STD	MSTR	WT/STD	UNIT
Packed in a Hanging Pouch							
BLH3612	21750	3/16"	12"	1	6	0.110#	Ea
BLH1412	21752	1/4"	12"	1	6	0.170#	Ea
BLH5612	21754	5/16"	12"	1	6	0.250#	Ea
BLH3812	21756	3/8"	12"	1	6	0.340#	Ea
BLH1212	21758	1/2"	12"	1	6	0.540#	Ea
BLH1418	21760	1/4"	18"	1	6	0.260#	Ea
BLH5618	21762	5/16"	18"	1	6	0.390#	Ea
BLH3818	21764	3/8"	18"	1	6	0.550#	Ea
BLH1218	21766	1/2"	18"	1	6	0.870#	Ea
BLH1424	21770	1/4"	24"	1	6	0.350#	Ea
BLH5624	21772	5/16"	24"	1	6	0.530#	Ea
BLH3824	21774	3/8"	24"	1	6	0.750#	Ea
BLH1224	21776	1/2"	24"	1	6	1.220#	Ea
BLH1430	21778	1/4"	30"	1	6	0.380#	Ea
BLH3830	21780	3/8"	30"	1	6	0.880#	Ea
BLH1442	21782	1/4"	42"	1	6	0.610#	Ea
BLH3842	21784	3/8"	42"	1	6	1.310#	Ea

TECH TALK

Electrician's Flex-A-Bits are specifically designed to facilitate fishing wires and cables through walls and ceilings. A self feeding screw point is permanently brazed to flexible shafts.

