



Bare Ground Clamps PC 5560

Bare ground clamps are used to connect bare copper wire to water pipe, rebar, ground rod or copper water tubing for grounding. Fittings are UL listed and cast from high strength, highly conductive copper alloy with steel, brass or bronze screws.

- UL Listed
- Pressure Cast or Bronze
- Bonding or Grounding
- With Steel, Stainless Steel, Brass or Bronze Screws

CAT NO	UPC	WIRE RANGE	DESCRIPTION	SCREW TYPE	PIPE SIZE	STD	MSTR	WT/STD	UNIT
20B*	10005	8 Sol to 2 Str	Prsr Cast Brs Plated	Steel	1/2 to 1"	25	250	3.83#	C
20M	10010	8 Sol to 2 Str	Prsr Cast Mlbl Finish	Steel	1/2 to 1"	25	250	4.40#	C
25	10015	10 Sol to 2 Str	Bronze	Steel	1/2 to 1"	25	250	4.48#	C
DB25	67500	10 Sol to 2 Str	Bronze Direct Burial	Bronze	1/2 to 1"	25	250	4.79#	C
DLI25	28090	10 Sol to 2 Str	Bronze Direct Burial Lay in Feature	Stainless Steel	1/2 to 1"	25	250	4.79#	C
DB25 and DLI25 Approved For Steel 4/6/8 Rebar									
DB2538	67503	10 Sol to 2 Str	Bronze Direct Burial	Bronze	1/2 to 1"	25	250	4.45#	C
DB2538 Dual Rated Suitable For Pipe or Steel Rebar 3/8 to 1" (#3 - #8). Accommodates Steel Rebar Without Disassembly									
PL25	56470	10 Sol to 2 Str	Bronze	Brass	1/2 to 1"	25	250	4.85#	C
27	10025	10 Sol to 2 Str	Bronze	Steel	1-1/4 to 2"	5	50	2.18#	C
DB27	67502	10 Sol to 2 Str	Bronze Direct Burial	Bronze	1-1/4 to 2"	5	50	2.13#	C
DLI27	28092	10 Sol to 2 Str	Bronze Direct Burial Lay in Feature	Stainless Steel	1-1/4 to 2"	5	50	2.13#	C
1001	10027	10 Sol to 2 Str	Bronze	Steel	2-1/2 to 4"	5	5	5.07#	C
1002	10028	10 Sol to 2 Str	Bronze	Steel	4-1/2 to 6"	5	5	9.12#	C

* Non UL Approved



Armored Ground Clamps PC 5560

Used to connect armored cable to water pipe for grounding. Special pressure bar grips armored cable insulation to decrease chances of grounding conductor being pulled out. Cast from high strength, highly conductive copper alloy.

- UL Listed
- Pressure Cast or Bronze
- Bonding or Grounding
- With Steel or Stainless Steel Screws

CAT NO	UPC	WIRE RANGE	DESCRIPTION	SCREW TYPE	PIPE SIZE	STD	MSTR	WT/STD	UNIT
21B*	10030	8 Sol to 4 Str	Prsr Cast Brs Plated	Steel	1/2 to 1"	25	250	5.09#	C
21M	10035	8 Sol to 4 Str	Prsr Cast Mlbl Finish	Steel	1/2 to 1"	25	250	5.09#	C
26	10040	8 Sol to 4 Str	Bronze	Steel	1/2 to 1"	25	250	5.83#	C
DLI26	28091	8 Sol to 4 Str	Bronze Lay in Feature	Stainless Steel	1/2 to 1"	25	250	5.63#	C
26SWV	10042	10 Sol to 6 Str	Bronze Swivel Type	Steel	1/2 to 1"	25	125	9.33#	C
26SWV Includes a pressure bar that swings 360° for easy adjustment									
28	10045	8 Sol to 4 Str	Bronze	Steel	1-1/4 to 2"	25	250	11.63#	C
28SWV	10046	10 Sol to 6 Str	Bronze swivel Type	Steel	1-1/4 to 2"	5	5	3.05#	C
28SWV Includes a pressure bar that swings 360° for easy adjustment									
1102*	10047	8 Sol to 4 Str	Bronze	Steel	2-1/2 to 4"	5	5	6.60#	C
1103*	11048	8 Sol to 4 Str	Bronze	Steel	4-5-6"	5	5	9.92#	C

* Non UL Approved

