

Speed D Feed Bits PC 6355



- Fast Heavy Duty Power Boring
- Tapered Back For Easy Back Out
- Universal 7/16" Shank, 5" OA Length
- Replaceable Double Ended Self Feeding Point

- Open Design For No Clog Fast Chip Removal
- Precision Angled Surface For Smoother Cuts
- Caution! Always Wear Eye Protection

Speed D Feed multi-spur wood boring bits are ideal for boring large holes quickly - from 1" through 4-5/8". This bit is especially suited to electricians and plumbers.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|---------|-------|---------|-----|------|--------|------|
| SDF100 | 21900 | 1" | 1 | 6 | 0.438# | Ea |
| SDF118 | 21901 | 1-1/8" | 1 | 6 | 0.469# | Ea |
| SDF114 | 21902 | 1-1/4" | 1 | 6 | 0.500# | Ea |
| SDF138 | 21903 | 1-3/8" | 1 | 6 | 0.500# | Ea |
| SDF112 | 21904 | 1-1/2" | 1 | 6 | 0.563# | Ea |
| SDF134 | 21905 | 1-3/4" | 1 | 6 | 0.625# | Ea |
| SDF200 | 21906 | 2" | 1 | 6 | 0.719# | Ea |
| SDF218 | 21907 | 2-1/8" | 1 | 6 | 0.813# | Ea |
| SDF214 | 21908 | 2-1/4" | 1 | 6 | 0.938# | Ea |
| SDF2916 | 21909 | 2-9/16" | 1 | 6 | 1.063# | Ea |
| SDF300 | 21910 | 3" | 1 | 6 | 1.500# | Ea |
| SDF358 | 21911 | 3-5/8" | 1 | 6 | 2.000# | Ea |
| SDF458 | 21912 | 4-5/8" | 1 | 6 | 3.500# | Ea |

Replacement Screw Points

| | | | | | | |
|--------|-------|---------------------------------------|---|---|-------|----|
| SDF14S | 21913 | 1/4 x 2-1/2" (For 1" thru 2-9/16") | 1 | 6 | 0.01# | Ea |
| SDF14L | 21914 | 1/4 x 2-3/4" (For 3" thru 4-5/8") | 1 | 6 | 0.01# | Ea |

Flex-A-Bit PC 6360



- Self Feeding Point
- Flexible Spring Steel Shaft
- Display Pack
- Caution! Always Wear Eye Protection

Flex A Bits are used to drill within walls and are able to reach normally inaccessible areas through a small opening. After (drilling) through a stud or header, a wire is attached to the fish hole in the flute and the drill is retracted pulling the wire through. The FG357 Flex A Guide tool aids in positioning the bit.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|------------|-----|------|--------|------|
| FB3854 | 37000 | 3/8 x 54" | 1 | 6 | 0.500# | Ea |
| FB3872 | 37005 | 3/8 x 72" | 1 | 6 | 0.640# | Ea |
| FB5054 | 37010 | 1/2 x 54" | 1 | 6 | 0.530# | Ea |
| FB5072 | 37015 | 1/2 x 72" | 1 | 6 | 0.680# | Ea |
| FB9654 | 37030 | 9/16 x 54" | 1 | 6 | 0.540# | Ea |
| FB9672 | 37035 | 9/16 x 72" | 1 | 6 | 0.680# | Ea |
| FB7554 | 37020 | 3/4 x 54" | 1 | 6 | 0.950# | Ea |
| FB7572 | 37025 | 3/4 x 72" | 1 | 6 | 1.220# | Ea |

Flex-A-Bit Tool

| | | | | | | |
|-------|-------|-----|---|---|--------|----|
| FG357 | 37040 | All | 1 | 6 | 0.450# | Ea |
|-------|-------|-----|---|---|--------|----|



Pilot Drills & Accessories PC 6390



- 1/4" High Speed Drill Pilot
- Split Point Design
- Caution! Always Wear Eye Protection

Pilot drills are available with three flats or three notches. Set screws secure drill in arbor.

| CAT NO | UPC | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-------|---|-----|------|--------|------|
| VPD4 | 28540 | 4-1/2 x 1/4" Pilot Drill, Shank Ground 3 Sides | 1 | 10 | 0.050# | Ea |
| VPD4N | 28545 | 4-1/2 x 1/4" Pilot Drill, 3 Notches for Set Screw | 1 | 10 | 0.050# | Ea |
| VPD4S | 28550 | 3-1/16" Pilot Drill for V24K, V34, & V35P Arbors | 1 | 10 | 0.050# | Ea |
| VE121 | 28555 | 12" Extension for 7/16" Arbors | 1 | 1 | 0.800# | Ea |
| V44N | 28560 | Adapter Nut- Adapts Arbor with 1/2-20 threads to fit Hole Saw with 5/8-18 Threads | 1 | 1 | 0.650# | Ea |

See new products at Ihdottie.com

Dottie



Hole Saw Kits PC 6400



- Packed In Molded Cases
- Variable Pitch
- Bi-Metal Blades

- Caution! Always Wear Eye Protection

Hole saw kits are supplied with the most popular sizes for the electrician and plumber. The VP100 contains 9 popular electrical and plumbing saws, while the VP02E & VP08 are for the electrical conduit sizes. These kits contain the necessary arbors for all the hole saws.

| CAT NO | UPC | HOLE SAWS | ARBORS | STD | MSTR | WT/STD | UNIT |
|--------|-----|-----------|--------|-----|------|--------|------|
|--------|-----|-----------|--------|-----|------|--------|------|

Electrician's Hole Saw Kit (Contains 6 Electrical Conduit Sizes 1/2" - 2")

| | | | | | | | | |
|-------|-------|---|-------------|-------------|---|---|--------|----|
| VP02E | 28470 | VP14 7/8" VP18 1-1/8" VP22 1-3/8" VP28 1-3/4" VP32 2" | VP40 2-1/2" | V44 V45P | 1 | 1 | 2.700# | Ea |
|-------|-------|---|-------------|-------------|---|---|--------|----|



Maintenance Hole Saw Kit (Contains 9 Plumbing and Electrical Conduit Sizes 3/8" - 2")

| | | | | | | | | |
|-------|-------|--|---|-------------------------------------|---|---|--------|----|
| VP100 | 28472 | VP12 3/4" VP14 7/8" VP18 1-1/8" VP22 1-3/8" | VP24 1-1/2" VP28 1-3/4" VP32 2" VP36 2-1/4" VP40 2-1/2" | V24K V44 V45P VE121 Extension | 1 | 1 | 4.820# | Ea |
|-------|-------|--|---|-------------------------------------|---|---|--------|----|



Master Electrician's Hole Saw Kit (Contains 10 Electrical Conduit Sizes 1/2" - 4")

| | | | | | | | | |
|------|-------|---|---|-------------------------------------|---|---|--------|----|
| VP08 | 28474 | VP14 7/8" VP18 1-1/8" VP22 1-3/8" VP28 1-3/4" VP32 2" | VP40 2-1/2" VP48 3" VP58 3-5/8" VP66 4-1/8" VP72 4-1/2" | V24K V44 V45P VE121 Extension | 1 | 1 | 7.800# | Ea |
|------|-------|---|---|-------------------------------------|---|---|--------|----|



Kan-Cut Saws & Kits PC 6440



- Solid One Piece Construction
- Continuous Carbide Grit Edge

- Safer To Use
- New 5" Size
- Caution! Always Wear Eye Protection

Kan Cut saws effectively cut through stucco, lath and plaster or two sheets of 5/8" drywall in one pass to a depth of two inches. Fits most major brands Halo, Capri, Marco, Juno, Prescolite, Progress, Lithonia, Lightolier and others. Arbor not included use V45P.

| CAT NO | UPC | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-----|------|-----|------|--------|------|
|--------|-----|------|-----|------|--------|------|


Kan-Cut Fixture Saws

| | | | | | | | |
|------|-------|---|--------|---|--------|--------|----|
| 358C | 15960 |  | 3-5/8" | 1 | 1 | 0.880# | Ea |
| 425C | 15962 | | 4-1/4" | 1 | 1 | 1.060# | Ea |
| 438C | 15975 | | 4-3/8" | 1 | 1 | 1.080# | Ea |
| 550C | 81781 | | 5-1/2" | 1 | 1 | 1.500# | Ea |
| 638C | 15980 | | 6-3/8" | 1 | 1 | 1.990# | Ea |
| 658C | 15985 | | 6-5/8" | 1 | 1 | 2.050# | Ea |
| 678C | 15990 | 6-7/8" | 1 | 1 | 2.070# | Ea | |

| | | | | | | |
|------|-------|-------|---|---|--------|----|
| V45P | 28525 | Arbor | 1 | 1 | 0.500# | Ea |
|------|-------|-------|---|---|--------|----|

| CAT NO | UPC | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-----|-------------|-----|------|--------|------|
|--------|-----|-------------|-----|------|--------|------|

Kan-Cut Hole Saw Kits

| | | | | | | | |
|-------|-------|---|---|---|---|--------|----|
| KC100 | 17175 |  | One Ea: 638C Kan Cut, V45P Arbor & KC case | 1 | 1 | 3.830# | Ea |
| KC200 | 17180 | | One Ea: 425C, 638C Kan Cut, V45P Arbor & KC case | 1 | 1 | 4.280# | Ea |

Caution: Always wear eye protection. Penetrate the material at 90°. Hole saws may have a tendency to grab, causing injury. **Do Not Exceed 800 RPM.**