



Representative

**Catalog Number:** CF22-1  
**Product ID:** 7TAA267230R0004  
**UPC Number:** 78378609221  
**Status:** Active

Copper H-Type Compression Connector Main: 4, 2 Solid Copper, Main: 4 Stranded Copper

### North American Specifications (UNSPSC)

UNSPSC	39121448 Wire or cable compression connector
IGCC	4668 Wire or cable compression connector
Brand Name	Blackburn
Type	H-Type Compression Connector
Special Features	Efficient Design Requires Less Crimping Force. Full Length Tab makes Installation Easy. Installs with Standard Compression Tools and Dies. RUS Accepted.
Conductor Range	Tap .204-.258 inch
Material	Electrolytic Copper
Conductor Type	Crimp
Conductor Range (Main/Primary)	.368-.419 inch
Bolt Size	N/A
Mounting Hole Spacing	N/A

### Packaging

Inner Quantity	100
Inner Dimensions (inches)	4.75x5.25x3
Outer Quantity	600
Outer Dimensions (inches)	11.6x11.2x8
Weight Uom	6.31 lbs. per 100

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000520

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)