

## Safety Products

4x4™ - Best 

The ideal eyewear for workers who want high-end style and protection - at cost effective pricing. Strong, four-sided frame weighs just one ounce, providing both durable protection and comfort. Wrap-around frame supports dual polycarbonate lenses that come with an anti-scratch coating. Soft inset nosepiece helps ensure comfort and provides a snug, secure fit. Flexible temple tips relieve pressure behind the ear. Meets or exceeds ANSI Z87.1+ standards.

CAT NO	DESCRIPTION	UNIT	MSTR QTY
E4X4700	Black Frame/Clear Lens	10/Box	50
E4X4715	Black Frame/Grey Lens	10/Box	50
E4X4730	Black Frame/Amber Lens	10/Box	50
E4X4745	Black Frame/Clear Lens	10/Box	50
E4X4760	Black Frame/Blue Mirror Lens	10/box	50
E4X4700D	Black Frame/Clear Lens - Display Pack	1	10
E4X4715D	Black Frame/Grey Lens - Display Pack	1	10
E4X4730D	Black Frame/Amber Lens - Display Pack	1	10
E4X4745D	Black Frame/Clear Lens - Display Pack	1	10
E4X4760D	Black Frame/Blue Mirror Lens - Display Pack	1	10

4x4™ Polarized - Very Best 

CAT NO	DESCRIPTION	UNIT	MSTR QTY
E4X4775	Black Frame/Black Temple Tips/Gray Polarized Lens - Display Pack	1	10
E4X4775D	Black Frame/Black Temple Tips/Gray Polarized Lens - Display Pack	1	10

Cover2™ - Over-the-Glasses Design 

A revolutionary over-the-glasses design, Cover2 offers workers a compact, modern style that's significantly more attractive than traditional OTG products. One-piece polycarbonate lens offers a broad, unobstructed view of the workplace. Flexible temple tips work extremely well with prescription glasses, while minimizing pinching behind the head. Lightweight design, with adjustable-length temples, offers ultimate comfort with a custom fit. A cost-effective OTG solution that won't break the bank.

CAT NO	DESCRIPTION	UNIT	MSTR QTY
ECOV810	Black Temples/Clear Lens	1	10/Box
ECOV820	Black Temples/Gray Lens	1	10/Box

Wheelz™ - Safety Goggles 

Wheelz™ Goggles Provide Maximum Protection Against Dirt and Debris. Lightweight, compact frame is more comfortable than traditional goggles, which tend to be big and bulky. Frame is made of a soft, flexible material, providing additional comfort for long days on the job site. Whirlwind ventilation system minimizes fogging by circulating air through the optical chamber. Elastic head strap can easily be adjusted to ensure a safe, snug fit - regardless of the worker's head size. Available in 3.0 and 5.0 IR Filter versions.

CAT NO	DESCRIPTION	UNIT	MSTR QTY
EWHE925	Clear Frame/Clear Lens	1	10/Box
EWHE935	Black Frame/Gray Lens	1	10/Box

TruAir™ - Disposable Respirator - Better and Best 

TruAir N95 particulate respirators offer 95% filtration against aerosols free of oils below PEL. Economically priced to fit any budget. Widely accepted design that encourages compliance. Large, molded shell that helps to reduce breathing resistance, minimizing end-user fatigue. Non-latex, elastic head straps, plus an adjustable nosepiece, provide a safe, secure fit. Available with an exhalation vent that reduces hot air buildup; makes breathing easier.

CAT NO	DESCRIPTION	UNIT	MSTR QTY
MSK20	N95 Particulate Respirator 95% filtration against aerosols free of oils below PEL.		20/Box
MSK10	N95 Particulate Respirator with Vent 95% filtration against aerosols free of oils below PEL.		10/Box


## Dust Mask

**CAUTION:** Do Not Use As Protection From; Asbestos, Silica or Cotton Dust, Toxic Dust, Fumes, Mists, Gas or Vapor. **NOT TO BE USED IN SPRAY PAINT OPERATIONS!**

CAT NO	DESCRIPTION	UNIT	MSTR QTY
MSK50	General Purpose Dust Mask	50	500/Box
MSK55	General Purpose Dust Mask (5 pack)	12 packs	24 packs

## Ear Plugs - Better and Best

Tested by an independent, NVLAP accredited laboratory - 31 db NRR - one of the highest rated earplugs available!. Non-allergenic polyurethane formula is extraordinarily soft and comfortable. Self adjusting design exerts very little pressure on the ear canal.

CAT NO	DESCRIPTION	UNIT	MSTR QTY
MLE100	Corded, Tapered, Blue Polyurethane Earplugs 	100 Pair	100 Pair
MLE200	Tapered, Blue Polyurethane Earplugs	200 Pair	200 Pair

