



Rotating cap
for precise turning and control with fingertip

Precision handle
high quality plastic, cadmium free

Molded on tapered handle
allows rapid rotation

High performance blades
chrome-vanadium-molybdenum steel, Hard chrome finished

Tip
precision ground for exact fit, hard chromed non-slip surface

Wiha Long Life Precision Series



[SHOP](#)

260 Slotted Screwdriver, With Precision Handle
Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26008	.80	1/32	40	1.6	0.16	.01	120	4.7	.02	10
26010	1.0	.039	40	1.6	0.18	.01	120	4.7	.02	10
26012	1.2	3/64	40	1.6	0.20	.01	120	4.7	.02	10
26015	1.5	1/16	40	1.6	0.25	.01	120	4.7	.02	10
26018	1.8	.070	40	1.6	0.30	.01	120	4.7	.02	10
26020	2.0	5/64	40	1.6	0.40	.02	120	4.7	.02	10
26022	2.0	5/64	50	2.0	0.40	.02	145	5.7	.02	10
26023	2.0	5/64	100	3.9	0.40	.02	180	7.1	.03	10
26025	2.5	3/32	50	2.0	0.40	.02	145	5.7	.03	10
26027	2.5	3/32	100	3.9	0.40	.02	195	7.7	.03	10
26028	2.5	3/32	150	6.0	0.40	.02	245	9.6	.04	10
26030	3.0	1/8	50	2.0	0.50	.02	145	5.7	.03	10
26032	3.0	1/8	60	2.4	0.50	.02	170	6.7	.04	10
26033	3.0	1/8	100	3.9	0.50	.02	210	8.3	.04	10
26034	3.0	1/8	150	5.9	0.50	.02	260	10.2	.05	10
26035	3.5	9/64	60	2.4	0.60	.02	170	6.7	.05	10
26040	4.0	5/32	60	2.4	0.80	.03	170	6.7	.05	10
26041	4.0	5/32	100	3.9	0.80	.03	210	8.3	.06	10
26042	4.0	5/32	150	5.9	0.80	.03	260	10.2	.07	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26090 6 Piece Precision Slotted Set

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.

Item No.		lbs.
26090	Slotted:	
	1.5, 2.0 x 40mm	.27
	2.5, 3.0 x 50mm	
	3.5, 4.0 x 60mm	



[SHOP](#)

26099 8 Piece Precision Slotted Set

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. In canvas storage pouch

Item No.		lbs.
26099	Slotted: 1.0, 1.2, 1.5, 2.0 x 40mm	
	2.5, 3.0 x 50mm, 3.5, 4.0 x 60mm	.54