








FM9™ Aluminum Unilet® Conduit Bodies, Covers and Gaskets

For use with Rigid Steel, Rigid Aluminum and IMC Conduit.

| Appleton FM9 Conduit Bodies * ‡ | | | | |
|---------------------------------|---|---|--|---|
| Hub Size (Inches) | C | LB | LL | LR |
| |  |  |  |  |
| 1/2 | C19 | LB19 | LL19 | LR19 |
| 3/4 | C29 | LB29 | LL29 | LR29 |
| 1 | C39 | LB39 | LL39 | LR39 |
| 1-1/4 | C49 | LB49 | LL49 | LR49 |
| 1-1/2 | C59 | LB59 | LL59 | LR59 |
| 2 | C69 | LB69 | LL69 | LR69 |
| 2-1/2 | C789 | LB789 | LL789 | LR789 |
| 3 | C889 | LB889 | LL889 | LR889 |
| 3-1/2 | C989 | LB989 | LL989 | LR989 |
| 4 | C1089 | LB1089 | LL1089 | LR1089 |
| Hub Size (Inches) | T | TB | X | |
| |  |  |  | |
| 1/2 | T19 | TB19 | X19 | |
| 3/4 | T29 | TB29 | X29 | |
| 1 | T39 | TB39 | X39 | |
| 1-1/4 | T49 | TB49 | - | |
| 1-1/2 | T59 | TB59 | - | |
| 2 | T69 | TB69 | - | |
| 2-1/2 | T789 | - | - | |
| 3 | T889 | - | - | |
| 3-1/2 | T989 | - | - | |
| 4 | T1089 | - | - | |

* Refer to following page for Wiring Capacity Tables
 ‡ PVC coating available on all FM9 bodies. Add suffix -PVC to catalog number.