



Conduit Bushings for Rigid Metal Conduit and IMC

	Catalog Number	Trade Size (Inches)	Dimensions in Inches/Millimeters		Weight Lbs./Kgs. Per 100
			Diameter	Height	
Threaded Impact Resistant Plastic Bushing – 105 °C Temperature Rating					
	BBU50	1/2	1.06/26.9	0.41/10.4	0.60/0.27
	BBU75	3/4	1.31/33.3	0.41/10.4	0.80/0.36
	BBU100	1	1.56/39.6	0.56/14.2	1.50/0.68
	BBU125	1-1/4	1.91/48.5	0.56/14.2	2.30/1.04
	BBU150	1-1/2	2.19/55.6	0.56/14.2	3.00/1.36
	BBU200	2	2.69/68.3	0.63/16.0	4.00/1.81
	BBU250	2-1/2	3.19/81.0	0.72/18.3	7.80/3.54
	BBU300	3	3.84/97.5	0.75/19.1	10.00/4.54
	BBU350	3-1/2	4.34/110.2	0.75/19.1	13.00/5.90
	BBU400	4	4.84/122.9	0.78/19.8	11.00/4.99
Threaded Thermoplastic Bushing – 150 °C Temperature Rating					
	BBU50H	1/2	1.06/26.9	0.41/10.4	0.80/0.36
	BBU75H	3/4	1.31/33.3	0.41/10.4	0.90/0.41
	BBU100H	1	1.56/39.6	0.56/14.2	1.80/0.82
	BBU125H	1-1/4	1.91/48.5	0.56/14.2	2.80/1.27
	BBU150H	1-1/2	2.19/55.6	0.56/14.2	3.30/1.50
	BBU200H	2	2.69/68.3	0.63/16.0	4.40/2.00
	BBU250H	2-1/2	3.19/81.0	0.72/18.3	14.30/6.49
	BBU300H	3	3.84/97.5	0.75/19.1	11.00/4.99
	BBU350H	3-1/2	4.34/110.2	0.75/19.1	14.30/6.49
	BBU400H	4	4.84/122.9	0.78/19.8	18.70/8.48

COMMERCIAL PRODUCTS: RIGID AND IMC FITTINGS

Commercial Products