

Replacement Glands for Aluminum and Steel CG and CG90 Connectors

Suitable for use in:
 Class I, Division 2
 Class II, Division 1 and 2
 Class III
 NEMA 3R

Not to be used with stainless steel and nickel plated aluminum CG connectors

| Catalog Number | For Use With Straight Connectors | For Use With 90° Connectors | Cable Range (Inches) | Wt. Lbs./Kgs. Per 100 |
|--|----------------------------------|-----------------------------|----------------------|-----------------------|
| For Connectors with 3/8 Inch Hubs | | | | |
| CGG-221 | CG-1238 | CG90-1238 | 0.125—0.187 | 2.50/1.13 |
| CGG-222 | CG-1838 | CG90-1838 | 0.187—0.312 | 1.90/0.86 |
| CGG-223 | CG-3138 | CG90-3138 | 0.312—0.437 | 1.30/0.59 |
| For Connectors with 1/2 Inch Hubs | | | | |
| CGG-221 | CG-1250 | — | 0.125—0.187 | 2.50/1.13 |
| CGG-271 | — | CG90-1250 | 0.125—0.250 | 1.90/0.86 |
| CGG-222 | CG-1850 | — | 0.187—0.312 | 1.90/0.86 |
| CGG-272 | — | CG90-2550 | 0.250—0.375 | 1.30/0.59 |
| CGG-223 | CG-3150 | — | 0.312—0.437 | 1.30/0.59 |
| CGG-273 | CG-3750 | CG90-3750 | 0.375—0.500 | 1.90/0.86 |
| CGG-274 | CG-5050 | CG90-5050 | 0.500—0.625 | 1.30/0.59 |
| CGG-275 | CG-6250 | CG90-6250 | 0.625—0.750 | 1.00/0.45 |
| For Connectors with 3/4 Inch Hubs | | | | |
| CGG-271 | CG-1275 | — | 0.125—0.250 | 1.90/0.86 |
| CGG-272 | CG-2575 | — | 0.250—0.375 | 1.30/0.59 |
| CGG-325 | — | CG90-2575 | 0.250—0.375 | 1.30/0.59 |
| CGG-273 | CG-3775 | — | 0.375—0.500 | 1.90/0.86 |
| CGG-321 | — | CG90-3775 | 0.375—0.500 | 1.90/0.86 |
| CGG-274 | CG-5075 | — | 0.500—0.625 | 1.30/0.59 |
| CGG-322 | — | CG90-5075 | 0.500—0.625 | 1.30/0.59 |
| CGG-323 | CG-6275 | CG90-6275 | 0.625—0.750 | 1.00/0.45 |
| CGG-324 | CG-7575 | CG90-7575 | 0.750—0.875 | 1.00/0.45 |
| For Connectors with 1 Inch Hubs | | | | |
| CGG-321 | CG-37100 | — | 0.375—0.500 | 1.90/0.86 |
| CGG-322 | CG-50100 | — | 0.500—0.625 | 1.30/0.59 |
| CGG-323 | CG-62100 | — | 0.625—0.750 | 1.00/0.45 |
| CGG-374 | — | CG90-62100 | 0.625—0.750 | 1.00/0.45 |
| CGG-371 | CG-75100 | CG90-75100 | 0.750—0.875 | 2.90/1.32 |
| CGG-372 | CG-87100 | CG90-87100 | 0.875—1.000 | 2.50/1.13 |
| CGG-373 | CG-100100 | CG90-100100 | 1.000—1.125 | 2.20/1.00 |
| For Connectors with 1-1/4 Inch Hubs | | | | |
| CGG-371 | CG-75125 | — | 0.750—0.875 | 2.90/1.32 |
| CGG-425 | — | CG90-75125 | 0.750—0.875 | 2.90/1.32 |
| CGG-372 | CG-87125 | — | 0.875—1.000 | 2.50/1.13 |
| CGG-426 | — | CG90-87125 | 0.875—1.000 | 2.50/1.13 |
| CGG-421 | CG-100125 | CG90-100125 | 1.000—1.125 | 2.20/1.00 |
| CGG-422 | CG-112125 | CG90-112125 | 1.125—1.250 | 1.90/0.86 |
| CGG-423 | CG-125125 | CG90-125125 | 1.250—1.375 | 1.60/0.73 |
| CGG-424 | CG-137125 | CG90-137125 | 1.375—1.500 | 1.30/0.59 |



FITTINGS: CABLE AND CORD FITTINGS

Fittings

For Steel Backed Neoprene Sealing Gaskets and Steel Gasketed Sealing Locknuts, see Commercial Fittings.