

















Contender® Series Replacement Parts and Accessories

Class I, Division 1, Groups C, D
 Class I, Division 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III

Description		Catalog Number		
Push Button — Factory Sealed — Momentary Contact				
	10 Amp 600 Vac Heavy Duty 1/2" thread size (NPSM). Furnished with 1/2" to 3/4" enlarger, Weather Boot, Guard, Start, Stop and Blank Nameplates. Single Push Button	Universal 		
	Double Push Button	Universal 		
Push Button — Red Mushroom Head — Factory Sealed — Maintained Contact				
	10 Amp 600 Vac Heavy Duty 1/2" thread size (NPSM). Furnished with 1/2" to 3/4" enlarger and Emergency Stop Nameplate (guard not furnished). Single Push Button	Universal 		
Rectangular Button with Weather Boot				
	Furnished with Start, Stop and Blank Nameplates.	NBN-WB		
Nameplates for Rectangular Push Buttons				
	Blank	SNP-B-Q	Off	SNP-OFF-Q
	Forward	SNP-FWD-Q	On	SNP-ON-Q
	Jog	SNP-JOG-Q	Reverse	SNP-REV-Q
	Run	SNP-RUN-Q	Open	SNP-OPEN-Q
	Stop	SNP-SP-Q	Close	SNP-CLOSE-Q
	Start	SNP-ST-Q	Up	SNP-UP-Q
	Down	SNP-DOWN-Q	Test	SNP-TEST-Q
	Fast	SNP-FAST-Q	Low	SNP-LOW-Q
	Slow	SNP-SLOW-Q	High	SNP-HIGH-Q
	Raise	SNP-RAISE-Q		
	Lower	SNP-LOWER-Q		
	Reset	SNP-RESET-Q		
Push Button Replacement Locking Guards — Glass Reinforced Polypropylene — Gasketed				
	Maintained Mushroom Head Switch Guard <i>Has hole for 1/4" hasp.</i>	SMPB-LG		
	Single Guard (Maintained Mushroom Head Switch)	NPB-LG1		
	Single Guard	NPB-LG2		
	Double Guard	NPB-LG1-LL		
	Single Guard (No Lockout Holes)	NPB-LG2-LL		
	Double Guard (No Lockout Holes)	NPB-LG2-LL		
Push Button Securing Rod with Chain — Stainless Steel				
	For use with Single Guard Only	NBL-SR		
Mushroom Head Button with Weather Boot for Use with Momentary Contact — Gasketed				
	Black	NMRB-BL		
	Green	NMRB-GR		
	Red	NMRB-RE		

Controls

CONTROLS: HAZARDOUS LOCATION CONTROL STATIONS AND SWITCHES