





# EFS Non-Sealed Front Operated Tumbler Switches

## Explosionproof, Dust-Ignitionproof

Malleable Iron Body and Cover. Furnished with Internal Ground Screw.

Class I, Division 1 and 2, Groups C, D  
 Class II, Division 1 and 2, Groups E, F, G  
 Class III  
 NEMA 7CD, 9EFG

	Hub Size (Inches)	Switch	Dead-End	Catalog Number †	Feed-Thru	
<b>1-Gang</b>						
 <p><b>Dead-End</b></p>	<b>20 Amp — 120-277 Vac †</b>					
	1/2	1-Pole	EFS150-F1	EFSC150-F1		
	1/2	2-Pole	—	EFSC150-F2		
	1/2	3-Way	EFS150-F3W	EFSC150-F3W		
	1/2	4-Way	EFS150-F4W	EFSC150-F4W		
	3/4	1-Pole	EFS175-F1	EFSC175-F1		
	3/4	2-Pole	EFS175-F2	EFSC175-F2		
	3/4	3-Way	EFS175-F3W	EFSC175-F3W		
 <p><b>Feed-Thru</b></p>	<b>20 Amp — 120-277 Vac †</b>					
	3/4	1-Pole	EFS175-F13	EFSC175-F13		
	3/4	2-Pole	EFS175-F23	EFSC175-F23		
	<b>30 Amp — 120-277 Vac †</b>					
	3/4	1-Pole	EFS175-F13	EFSC175-F13		
	3/4	2-Pole	EFS175-F23	EFSC175-F23		
	<hr/>					
	<b>2-Gang</b>					
 <p><b>Dead-End</b></p>	<b>20 Amp — 120-277 Vac †</b>					
	1/2	1-Pole	EFS250-F1	EFSC250-F1		
	1/2	2-Pole	—	EFSC250-F2		
	1/2	3-Way	—	EFSC250-F3W		
	1/2	4-Way	—	EFSC250-F4W		
	3/4	1-Pole	EFS275-F1	EFSC275-F1		
	3/4	2-Pole	—	EFSC275-F2		
	3/4	3-Way	—	EFSC275-F3W		
 <p><b>Feed-Thru</b></p>	3/4	4-Way	—	EFSC275-F4W		
	1	2-Pole	EFS210-F2	EFSC210-F2		
	1	3-Way	EFS210-F3W	EFSC210-F3W		
	1	4-Way	EFS210-F4W	EFSC210-F4W		
	<b>30 Amp — 120-277 Vac †</b>					
	3/4	1-Pole	EFS275-F13	EFSC275-F13		
	3/4	2-Pole	—	EFSC275-F23		
	1	2-Pole	EFS210-F23	EFSC210-F23		

† For aluminum backbox and cover, add suffix -A.  
 † 20 Amp — 1 HP at 120 Vac and 2 HP at 240 Vac.  
 † 30 Amp — 2 HP at 120 Vac or 240 Vac.