









Mercmaster™ III Low Profile Compact Fluorescent Luminaire Accessories

Enclosed and Gasketed. For Hazardous and Wet Locations

Compact Fluorescent listed for simultaneous exposure to combustible dusts and flammable gases or vapors.

Item	Description	Catalog Number ③
White Polyester Reflectors		
 Standard Dome	For Globe Fixtures	
	Standard Dome 30° Angle	KR2-ST KR2-AN
 30° Angle Dome	For Glass Refractor Fixtures ❶	
	Standard Dome 30° Angle	CMR-4ST ② CMR-4AN ②
Prismatic Glass Globes — Heat-Resistant ③		
	Clear	VPGL-2HR
	Amber ④	VPGL-2AM
	Blue ④	VPGL-2BL
	Green ④	VPGL-2GR
	Red ④	VPGL-2RE
	Clear — 57/114 Watt ❷	VPGL-4HR
Closed Prismatic Glass Refractors — All Heat-Resistant ③		
	NEMA Type I	LPG-R1
	NEMA Type III	LPG-R3
	NEMA Type V	LPG-R5
Closed Prismatic Polymeric Refractors — Not Listed for Class I, Zone 2 Areas		
	NEMA Type II	LPRF-2CP
	NEMA Type III	LPRF-3CP
	NEMA Type IV	LPRF-4CP
	NEMA Type V	LPRF-5CP
Guards		
 Globe Guard	Globe Guard	KGU2
	 Glass Refractor Guard	Glass Refractor Guard
 Globe Guard for 57 W Only		Globe Guard — 57/114 W ❷

❶ Fixtures with refractors are not UL Listed when used with reflectors.

❷ Standard dome reflectors may interfere with bottom conduit entry if used with KPST and KPWB mounting hoods.

❸ Silicone or Teflon ❷ coated globes are available. Contact your local sales representative.

❹ Non hazardous rated globes for special applications.

❷ CSA Certification only.