

Contender® Series Factory Sealed Selector Switches


Explosionproof, Dust-Ignitionproof

10 Amp, 600 Vac Max. for Heavy Duty Use Momentary Contact. Furnished with Internal Ground Screw.


Class I, Division 1, Groups C, D
 Class I, Division 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 3, 7CD, 9EFG

Controls

CONTROLS: HAZARDOUS LOCATION CONTROL STATIONS AND SWITCHES

Selector Switches	Hub Size (Inches)	Description	Diagram			Catalog Number	
			Left	Center	Right	Dead-End	Feed-Thru
2 Position Selector Switches — 1-Gang † — Maintained Contact							
	1/2	2 Position, 2 Circuit		None		EDS11271	EDSC11271
	3/4		EDS21271			EDSC21271	
	1		EDS31271			EDSC31271	
	1/2	2 Position, 4 Circuits		None		EDS11272	EDSC11272
	3/4		EDS21272			EDSC21272	
	1		EDS31272			EDSC31272	


Nameplate: Hand—Auto

3 Position Selector Switches — 1-Gang † — Maintained Contact							
	1/2	3 Position, 2 Circuit				EDS11273	EDSC11273
	3/4		EDS21273			EDSC21273	
	1		EDS31273			EDSC31273	
	1/2	3 Position, 4 Circuits				EDS11274	EDSC11274
	3/4		EDS21274			EDSC21274	
	1		EDS31274			EDSC31274	

Nameplate: Hand—Off—Auto

	Thread Size (In., NPSM)	Description	Diagram			Switch Catalog Number	
			Left	Center	Right	Assembly Only	Assembly w/ Cover

EDKB Selector Switch Operator/Switch Assembly † — Maintained Contact



Nameplate: Hand—Auto

2 Position							
1/2	2 Position, 2 Circuit		None		SSBA1-2Q	EDKB-12	
1/2						SSBA2-2Q	EDKB-35



Nameplate: Hand—Off—Auto

3 Position							
1/2	3 Position, 2 Circuit				SSBA1-3Q	EDKB-102	
1/2						SSBA2-3Q	EDKB-345

EDKB Selector Switch Operator/Switch Assembly ‡ — Modified Operations — 3 Position

Momentary contact right position. Spring return to center. Maintained contact left position.

Note: Standard legend plate reads Hand/Off/Auto



2 Circuit

1/2	3 Position, 2 Circuit				SSBAS-1-3	EDKB-102-S634
1/2						SSBAS-2-3

Momentary contact left position. Spring return to center. Maintained contact right position.

Note: Standard legend plate reads Hand/Off/Auto



4 Circuit

1/2	3 Position, 2 Circuit				SSBASL-1-3	EDKB-102-S635
1/2						SSBASL-2-3

Momentary contact right position. Spring return to center. Maintained contact left position.

Note: Standard legend plate reads Hand/Off/Auto

1/2	3 Position, 4 Circuits				SSBASRA-2-3	EDKB-345-S636
-----	------------------------	--	--	--	-------------	---------------

† Malleable Iron Body and Cover. For Aluminum Body and Cover, add suffix - SA.

‡ For Aluminum Cover only, add suffix - A.

◇ Supplied as standard with maintained contact selector switches. Specify catalog number from nameplate listings if other than standard nameplate is desired.