



Conduit Bushings for Rigid Metal Conduit and IMC

COMMERCIAL PRODUCTS: RIGID AND IMC FITTINGS

Commercial Products

	Catalog Number	Trade Size (Inches)	Dimensions in Inches/Millimeters		Weight Lbs./Kgs. Per 100
			Diameter	Height	
Threadless Bushings – Insulated – 150 °C Temperature Rating – Malleable Iron, Zinc Electroplated					
	BU50SI	1/2	1.19/30.2	0.50/12.7	4.00/1.81
	BU75SI	3/4	1.44/36.6	9.06/230.1	6.00/2.72
	BU100SI	1	1.75/44.5	0.63/16.0	9.00/4.08
	BU125SI	1-1/4	2.13/54.1	0.75/19.1	10.00/4.54
	BU150SI	1-1/2	2.31/58.7	0.88/22.4	18.00/8.16
	BU200SI	2	2.81/71.4	0.94/23.9	25.00/11.34
	BU250SI	2-1/2	3.38/85.9	1.00/25.4	40.00/18.14
	BU300SI	3	4.06/103.1	1.13/28.7	55.00/24.95
	BU350SI	3-1/2	4.50/114.3	1.19/30.2	59.00/26.76
	BU400SI	4	5.19/131.8	1.31/33.3	90.00/40.82
Threaded Capped Bushings – Malleable Iron, Zinc Electroplated, Polyethylene Cap					
	BUC50	1/2	1.03/26.2	0.38/9.7	3.00/1.36
	BUC75	3/4	1.25/31.8	0.44/11.2	5.00/2.27
	BUC100	1	1.56/39.6	0.50/12.7	8.00/3.63
	BUC125	1-1/4	2.00/50.8	0.63/16.0	12.00/5.44
	BUC150	1-1/2	2.16/54.9	0.63/16.0	17.00/7.71
	BUC200	2	2.63/66.8	0.63/16.0	20.00/9.07
	BUC250	2-1/2	3.19/81.0	0.75/19.1	40.00/18.14
	BUC300	3	3.81/96.8	0.94/23.9	52.00/23.59
	BUC350	3-1/2	4.44/112.8	0.94/23.9	76.00/34.47
	BUC400	4	4.94/125.5	1.06/26.9	114.00/51.71
BUC500	5	6.00/152.4	1.19/30.2	149.00/67.59	
BUC600	6	7.38/187.5	1.31/33.3	250.00/113.40	