

FSQX 30 Amp Receptacles with Interlocked Switch and Cover

Explosionproof, Dust-Ignitionproof

Raintight Screw Cap Receptacle Cover—Interlocked Switch and Cover Safety Construction.

Class I, Division 1 and 2 Groups B, C, D
 Class II, Division 1 and 2 Groups F, G
 Class III
 NEMA 7BCD, 9FG

Type	Wire/Pole	Hub Size (Inches)	Catalog Number
------	-----------	-------------------	----------------

FSQX Receptacles

Furnished with four hubs and three close-up plugs. Supplied with 1" to 3/4" reducers.



2-Pole Switch rated at 30 Amp 2 HP, 120 Vac 5 HP, 240 Vac 10 HP, 480 Vac 15 HP, 600 Vac	2W, 3P	1	FSQX3023-100
3-Pole Switch rated at 30 Amp 3 HP, 120 Vac 7.5 HP, 240 Vac 15 HP, 480 Vac 20 HP, 600 Vac	3W, 4P	1	FSQX3034-100

Type	Wire/Pole	Cable Dia., Inches Min. — Max.	Catalog Number
------	-----------	--------------------------------	----------------

FP Plugs for Use with Receptacles Above

Furnished with cable grip and rubber bushing. Solder well wire terminals. Pressure terminal for grounding.



Plug amperes match receptacle ratings	2W, 3P	.75 to .875	FP-3023
	3W, 4P	.75 to .875	FP-3034

Dimensions

