







NEC 6x8x Series C, LB, UB Mogul Unilet® Conduit Outlet Bodies

For use with Threaded Rigid Metal Conduit and IMC. Complete with Assembled Cover and Neoprene Gasket.

Type	Hub Size (Inches)	Body, Cover & Gasket			Cover & Gasket	
		Malleable Iron	Aluminum	Gasket Only	Malleable Iron	Aluminum
C NEC 8X						
 <p>1" - 2"</p>	1	BC100-M	BC100-A	BG100	BKG100-M	BKG100-A
	1-1/4	BC125-M ‡	BC125-A ‡	BGC125	BKGC125-M	BKGC125-A
	1-1/2	BC150-M ‡	BC150-A ‡	BG150	BKG150-M	BKG150-A
	2	BC200-M ‡	BC200-A ‡	BGC200	BKGC200-M	BKGC200-A
 <p>2-1/2" - 4"</p>	2-1/2	BC250-M ‡	BC250-A ‡	BGC250	BKGC250-M	BKGC250-A
	3	BC300-M ‡	BC300-A ‡	BGC300	BKGC300-M	BKGC300-A
	3-1/2	BC350-M ‡	BC350-A ‡	BGC350	BKGC350-M	BKGC350-A
	4	BC400-M ‡	BC400-A ‡	BGC400	BKGC400-M	BKGC400-A
LB NEC 6X						
 <p>1" - 2"</p>	1	BLB100-M	BLB100-A	BG100	BKG100-M	BKG100-A
	1-1/4	BLB125-M ‡	BLB125-A ‡	BGL125	BKGL125-M	BKGL125-A
	1-1/2	BLB150-M ‡	BLB150-A ‡	BG150	BKG150-M	BKG150-A
	2	BLB200-M ‡	BLB200-A ‡	BGL200	BKGL200-M	BKGL200-A
 <p>2-1/2" - 4"</p>	2-1/2	BLB250-M ‡	BLB250-A ‡	BGL250	BKGL250-M	BKGL250-A
	3	BLB300-M ‡	BLB300-A ‡	BGL300	BKGL300-M	BKGL300-A
	3-1/2	BLB350-M ‡	BLB350-A ‡	BGL350	BKGL350-M	BKGL350-A
	4	BLB400-M ‡	BLB400-A ‡	BGL400	BKGL400-M	BKGL400-A
UB NEC 6X						
 <p>1" - 2"</p>	1	BUB100-M	BUB100-A	BG100	BKG100-M	BKG100-A
	1-1/4	BUB125-M ‡	BUB125-A ‡	BGL125	BKGL125-M	BKGL125-A
	1-1/2	BUB150-M ‡	BUB150-A ‡	BG150	BKG150-M	BKG150-A
	2	BUB200-M ‡	BUB200-A ‡	BGL200	BKGL200-M	BKGL200-A
 <p>2-1/2" - 4"</p>	2-1/2	BUB250-M ‡	BUB250-A ‡	BGL250	BKGC250-M	BKGC250-A
	3	BUB300-M ‡	BUB300-A ‡	BGL300	BKGU300-M	BKGU300-A
	3-1/2	BUB350-M ‡	BUB350-A ‡	BGL350	BKGC350-M	BKGC350-A
	4	BUB400-M ‡	BUB400-A ‡	BGL400	BKGU400-M	BKGU400-A

‡ Roller Feature.