

MD2SR Factory Sealed Interlocked Switched Receptacles

Dead Front Interlocked Construction; No External Seals Required.

Class I, Division 2, Groups B, C, D
 Class II, Division 1 and 2, Groups F, G
 Class III
 Class I, Zone 2, Group IIC T3
 NEMA 3*, 3R*, 4*, 4X*, 9FG, 12

Amp	Wires/Poles	Max HP	Fusing *	Catalog Number **	Mating Plug
30	2W, 3P	3 HP @ 240 Vac	Non-Fused	MD2SR3023U	ACP3023BC
			Fused	MD2SR3023F	
	3W, 4P	20 HP @ 600 Vac 30 HP @ 600 Vac	Non-Fused	MD2SR3034U	ACP3034BC
			Fused	MD2SR3034F	
60	2W, 3P	7.5 HP @ 240 Vac 10 HP @ 240 Vac	Non-Fused	MD2SR6023U	ACP6023BC
			Fused	MD2SR6023F	
	3W, 4P	50 HP @ 600 Vac	Non-Fused	MD2SR6034U	ACP6034BC
			Fused	MD2SR6034F	
100	2W, 3P	10 HP @ 240 Vac	Non-Fused	MD2SR1023U	ACP1023CD
			Fused	MD2SR1023F	
	3W, 4P	50 HP @ 600 Vac	Non-Fused	MD2SR1034U	ACP1034CD
			Fused	MD2SR1034F	

ACP Plugs for MD2SR Receptacles

Cable Dia. (Inches)	30 Amp		60 Amp		100 Amp	
	2W, 3P	3W, 4P	2W, 3P	3W, 4P	2W, 3P	3W, 4P
.390 to 1.375	ACP3023BC	ACP3034BC	ACP6023BC	ACP6034BC	—	—
.875 to 1.906	—	—	—	—	ACP1023CD	ACP1034CD



CPH Plugs for MD2SR Receptacles

Cable Dia. (Inches)	30 Amp		60 Amp		100 Amp	
	2W, 3P	3W, 4P	2W, 3P	3W, 4P	2W, 3P	3W, 4P
.390 to 1.375	CPH3023BC	CPH3034BC	CPH6023BC	CPH6034BC	—	—



• Flip cover suitable for NEMA 3, 3R only.

▼ NEMA 4 rating maintained with Appleton NEMA 4 plug installed. Select screw cover for 4, 4X. Both covers are included with product.

* Fused units contain fuse holders; fuses not included.

‡ For auxiliary switch: one normally opened, one normally closed, add suffix **-AUX**.

† For special polarization add **-P4**.