

Mercmaster™ III Induction Luminaire Fixture Units

Enclosed and Gasketed. For Hazardous and Adverse Locations

55W, 85W, 165W
 Class I, Division 2, Groups A, B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 NEMA 4X

55W, 85W
 Class I, Zone 2
 AEx nA nR, IIC
 Ex nA nR IIC

165W
 Class I, Zone 2
 AEx nR, IIC
 Ex nR IIC

Fixture Units – Less Mounting Hoods

	Type	Frequency	Lamp Watts	Fixture Unit Catalog Number	Add Voltage Suffixes	
					120 V	277 V
Globe 	Induction	50/60 Hz	55	MLBRG355Q	-A1	-A6
Globe 	Induction	50/60 Hz	85	MLBRG485Q	-A1	-A6
Globe 	Induction	50/60 Hz	165	KPB165QG4	-A1	-A6
Enclosed Reflector/Lens 	Induction	50/60 Hz	165	KPB165QRL	-A1	-A6
Type 2 Refractor 	Induction	50/60 Hz	165	KPB165QJ2	-A1	-A6
Type 5 Refractor	Induction	50/60 Hz	165	KPB165QJ5	-A1	-A6

Lighting

LIGHTING: ENCLOSED AND GASKETED – AREA – LED/INDUCTION